This document was generated on 03/10/2023


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** 2153431225

**Status:** Active

**Overview:** Off-the-Shelf Pre-Crimped Leads

**Description:** Pre-Crimped Lead Mini-Fit Jr. Male-to-Pigtail, Gold (Au) Plating, 450.00mm Length, 16 AWG, Black



*Series image - Reference only*

**Documents:**

Drawing (PDF)
Datasheet (PDF)
RoHS Certificate of Compliance (PDF)

**General**

| | |
|---|---|
| Product Family | Cable Assemblies |
| Series | 215343 |
| Application | Power, Wire-to-Wire |
| Assembly Configuration | Pre-crimped Lead Only |
| Connector to Connector | Mini-Fit Jr. Term-to-Pigtail |
| Overview | Off-the-Shelf Pre-Crimped Leads |
| Product Name | Mini-Fit Jr. |
| Taxonomy | Power and Signal Cable Assembl |
| UPC | 193264560486 |

**Physical**

| | |
|---|---|
| Cable Length | 450.00mm |
| Circuits (Loaded) | 1 |
| Color - Resin | Black |
| Gender | Male-Pigtail |
| Material - Metal | Brass |
| Material - Plating Mating | Gold |
| Material - Plating Termination | Tin |
| Net Weight | 10.105/g |
| Packaging Type | Bag |
| Single Ended | Yes |
| Termination Interface: Style | Crimp or Compression |
| Wire Insulation Diameter | 1.80-3.10mm |
| Wire Size AWG | 16 |
| Wire/Cable Type | UL 1015 |

**Electrical**

| | |
|---|---|
| Current - Maximum per Contact | 9.0A |
| Voltage - Maximum | 600V |

**Material Info**

**Reference - Drawing Numbers**

| | |
|---|---|
| Sales Drawing | 2153431221-000 |

**EU ELV**
**Not Relevant**

**EU RoHS** **China RoHS**
**Compliant**

**REACH SVHC**
Not Contained per - D(2022)9120-DC (17 Jan 2023)

**Halogen-Free Status**
**Not Low-Halogen**

For more information, please visit Contact US

| | |
|---|---|
| China ROHS | Green Image |
| ELV | Not Relevant |
| RoHS Phthalates | Not Contained |

**Search Parts in this Series**
215343 Series

**Use With**
Mini-Fit Jr. Plug Housing 5559 <br>Mini-Fit BMI Plug Housing 42475

This document was generated on 03/10/2023

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**