





CKT	A	B
2	3.85	NA
4	6.85	3
6	9.85	6
8	12.85	9
10	15.85	12
12	18.85	15
14	21.85	18
16	24.85	21
18	27.85	24
20	30.85	27
22	33.85	30
24	36.85	33

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex	
mm		5:1							
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 760703 DRWN: VENKAS5 2023/03/30 CHK'D: VENKAS5 2023/08/24 APPR: MRAMAKRISHNA 2023/08/24				V HDR ASSY BANDO MICRO-FIT + SOLUTION	
ANGULAR TOL ± 0.5 °									
4 PLACES		±		INITIAL REVISION: DRWN: SMAHAJANSHET 2018/05/08 APPR: NCSR 2019/04/02				PRODUCT CUSTOMER DRAWING	
3 PLACES		±							
2 PLACES		± 0.25		DOCUMENT NUMBER 2068320000-SD				DOC TYPE	
1 PLACE		± 0.36						DOC PART	
0 PLACES		±		SERIES A3-SIZE 206832				REVISION C	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								SHEET NUMBER 1 OF 4	
THIRD ANGLE PROJECTION				DRAWING		MATERIAL NUMBER		CUSTOMER	
				A3-SIZE 206832		SEE TABLE		GENERAL MARKET	

- NOTES:
- HOSING MATERIAL: GLASS FILLED LIQUID CRYSTAL POLYMER, UL 94V-0, COLOR: BLACK
TERMINAL MATERIAL: HIGH COPPER ALLOY
 - FINISH:
OPTION 1: TIN OVER NICKEL OVERALL
OPTION 2: SELECT 15MICROINCH GOLD AND SELECT MATTE TIN OVER NICKEL.
OPTION 3: SELECT 30MICROINCH GOLD AND SELECT MATTE TIN OVER NICKEL.
 - PRODUCT SPECIFICATION : 2064600000-PS
 - TRAY PACK : 2068320000-PK
TAPE REEL PACK : 2068320001-PK
 - MATE WITH RECEPTACLE 206461
 - THIS PART CONFORMS TO CLASS 'B' REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.

DOCUMENT STATUS	P1	RELEASE DATE	2023/08/24 11:19:05
-----------------	----	--------------	---------------------

FORMAT: master-B-prod-A3
REVISION: 11
DATE: 2017/10/06

10		9		8		7		6		5		4	
TIN PLATING				30 MICROINCH GOLD				15 MICROINCH GOLD					
TRAY PACKAGING -2068320000-PK				TRAY PACKAGING -2068320000-PK				TRAY PACKAGING -2068320000-PK					
CKT	VRT HDR ASSY PN	POLARIZATION	COLOR	CKT	VRT HDR ASSY PN	POLARIZATION	COLOR	CKT	VRT HDR ASSY PN	POLARIZATION	COLOR		
2	2068320201	A	BLACK	2	2068320203	A	BLACK	2	2068320202	A	BLACK		
	2242460210	B	NATURAL		2242460212	B	NATURAL		2242460211	B	NATURAL		
	2242460220	C	RED		2242460222	C	RED		2242460221	C	RED		
	2242460230	D	BLUE		2242460232	D	BLUE		2242460231	D	BLUE		
	2242460240	E	YELLOW		2242460242	E	YELLOW		2242460241	E	YELLOW		
4	2068320401	A	BLACK	4	2068320403	A	BLACK	4	2068320402	A	BLACK		
	2242460410	B	NATURAL		2242460412	B	NATURAL		2242460411	B	NATURAL		
	2242460420	C	RED		2242460422	C	RED		2242460421	C	RED		
	2242460430	D	BLUE		2242460432	D	BLUE		2242460431	D	BLUE		
	2242460440	E	YELLOW		2242460442	E	YELLOW		2242460441	E	YELLOW		
6	2068320601	A	BLACK	6	2068320603	A	BLACK	6	2068320602	A	BLACK		
	2242460610	B	NATURAL		2242460612	B	NATURAL		2242460611	B	NATURAL		
	2242460620	C	RED		2242460622	C	RED		2242460621	C	RED		
	2242460630	D	BLUE		2242460632	D	BLUE		2242460631	D	BLUE		
	2242460640	E	YELLOW		2242460642	E	YELLOW		2242460641	E	YELLOW		
8	2068320801	A	BLACK	8	2068320803	A	BLACK	8	2068320802	A	BLACK		
	2242460810	B	NATURAL		2242460812	B	NATURAL		2242460811	B	NATURAL		
	2242460820	C	RED		2242460822	C	RED		2242460821	C	RED		
	2242460830	D	BLUE		2242460832	D	BLUE		2242460831	D	BLUE		
	2242460840	E	YELLOW		2242460842	E	YELLOW		2242460841	E	YELLOW		
10	2068321001	A	BLACK	10	2068321003	A	BLACK	10	2068321002	A	BLACK		
	2242461010	B	NATURAL		2242461012	B	NATURAL		2242461011	B	NATURAL		
	2242461020	C	RED		2242461022	C	RED		2242461021	C	RED		
	2242461030	D	BLUE		2242461032	D	BLUE		2242461031	D	BLUE		
	2242461040	E	YELLOW		2242461042	E	YELLOW		2242461041	E	YELLOW		
12	2068321201	A	BLACK	12	2068321203	A	BLACK	12	2068321202	A	BLACK		
	2242461210	B	NATURAL		2242461212	B	NATURAL		2242461211	B	NATURAL		
	2242461220	C	RED		2242461222	C	RED		2242461221	C	RED		
	2242461230	D	BLUE		2242461232	D	BLUE		2242461231	D	BLUE		
	2242461240	E	YELLOW		2242461242	E	YELLOW		2242461241	E	YELLOW		
14	2068321401	A	BLACK	14	2068321403	A	BLACK	14	2068321402	A	BLACK		
16	2068321601	A	BLACK	16	2068321603	A	BLACK	16	2068321602	A	BLACK		
18	2068321801	A	BLACK	18	2068321803	A	BLACK	18	2068321802	A	BLACK		
20	2068322001	A	BLACK	20	2068322003	A	BLACK	20	2068322002	A	BLACK		
22	2068322201	A	BLACK	22	2068322203	A	BLACK	22	2068322202	A	BLACK		
24	206832-2401	A	BLACK	24	206832-2403	A	BLACK	24	2068322402	A	BLACK		

TIN PLATING			
T&R PACKAGING -2068320001-PK			
CKT	VRT HDR ASSY PN	POLARIZATION	COLOR
2	206832-0221	A	BLACK
4	206832-0421		
6	206832-0621		
8	206832-0821		
10	206832-1021		
12	206832-1221		
14	206832-1421		
16	206832-1621		
18	206832-1821		
20	206832-2021		
22	206832-2221		
24	206832-2421		

15 MICROINCH GOLD			
T&R PACKAGING -2068320001-PK			
CKT	VRT HDR ASSY PN	POLARIZATION	COLOR
2	206832-0222	A	BLACK
4	206832-0422		
6	206832-0622		
8	206832-0822		
10	206832-1022		
12	206832-1222		
14	206832-1422		
16	206832-1622		
18	206832-1822		
20	206832-2022		
22	206832-2222		
24	206832-2422		

30 MICROINCH GOLD			
T&R PACKAGING -2068320001-PK			
CKT	VRT HDR ASSY PN	POLARIZATION	COLOR
2	206832-0223	A	BLACK
4	206832-0423		
6	206832-0623		
8	206832-0823		
10	206832-1023		
12	206832-1223		
14	206832-1423		
16	206832-1623		
18	206832-1823		
20	206832-2023		
22	206832-2223		
24	206832-2423		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS

mm

SCALE

1:1

GENERAL TOLERANCES (UNLESS SPECIFIED)

ANGULAR TOL ± 0.5 °

4 PLACES ±

3 PLACES ±

2 PLACES ± 0.25

1 PLACE ± 0.36

0 PLACES ±

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

CURRENT REV DESC:

EC NO: 760703
DRWN: VENKASS
CHK'D: VENKASS
APPR: MRAMAKRISHNA

2023/03/30
2023/08/24
2023/08/24

INITIAL REVISION:
DRWN: SMAHAJANSHET
APPR: NCSR

2018/05/08
2019/04/02

THIRD ANGLE PROJECTION

DRAWING

SERIES

A3-SIZE

206832

DOCUMENT NUMBER

2068320000-SD

DOC TYPE

PSD

DOC PART

000

REVISION

C

MATERIAL NUMBER

SEE TABLE

CUSTOMER

GENERAL MARKET

SHEET NUMBER

2 OF 4

mo

lex

V HDR ASSY BANDO
MICRO-FIT + SOLUTION

PRODUCT CUSTOMER DRAWING

DOCUMENT STATUS

P1

RELEASE DATE

2023/03/06

08:44:47

9

8

7

6

5

4

3

2

1

FORMAT: master-bb-prod-A3

REVISION: J

DATE: 2020/01/14

[illegible]

[illegible]