









SUGGESTED PCB LAYOUT
(COMPONENT SIDE)

SPECIFICATION

1 Material:
Insulator: PA66 (UL94V-0)
Contacts: Brass,Tin-plated
2 Contact resistance: ≤20mΩ
3 Insulation resistance: ≥1000MΩ
4 Rated voltage: 250 V AC DC
5 Rated current: 3.0 A AC DC
6 Withstand Voltage: 1000V AC/minute
7 Temperature Range: -25℃～ +85℃
8 Six deleterious substance content meet the environmental protection requirement

型号-线数 TYPE-Poles	尺寸Dimensions(mm)		
	A	B	C
XHB-2AW	2.50	7.50	6.00
XHB-3AW	5.00	10.00	8.50
XHB-4AW	7.50	12.50	11.00
XHB-5AW	10.00	15.00	13.50
XHB-6AW	12.50	17.50	16.00
XHB-7AW	15.00	20.00	18.50
XHB-8AW	17.50	22.50	21.00
XHB-9AW	20.00	25.00	23.50
XHB-10AW	22.50	27.50	26.00
XHB-11AW	25.00	30.00	28.50
XHB-12AW	27.50	32.50	31.00

REV	DESCRIPTION	REV. DRAWN	DATE
A	NEW RELEASE		

TOLERANCE	
.	±0.25
*.**	±0.15
*.***	±0.05

SCALE:
UNIT: mm
VIEW:

DRAW
CHECK
APPRO

XHB-弯针

TITLE: 2.50mm PITCH 90° WAFER

PART NO:

浙江博穆精密电子有限公司