
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST
AD	00

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	2	9.20 WAS 9.00, REV TABLE, REV SHT TOL	18NOV2002	RLK	LB
	3	CHANGE TABLE DIMENSIONS A	19MAR03	WGL	LB
	0	REV PER 0G3C-0616-03	02DEC03	RB	DR
	01	REVISED PER ECO-09-025699	08DEC2009	KK	AEG

1. UL 94V-0 RATED LCP.
2. TWO PIECES REQUIRED PER CONNECTOR ASSEMBLY.
3. BULK PACKAGED.
4. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI







	A	NO. OF POS.	PART NUMBER
	3.90	40	1-1445976-9
	3.80	38	1-1445976-8
	3.70	36	1-1445976-7
	3.60	34	1-1445976-6
OBSOLETE 4	3.50	32	1-1445976-5
	3.40	30	1-1445976-4
	3.30	28	1-1445976-3
	3.20	26	1-1445976-2
	3.10	24	1-1445976-1
	3.00	22	1-1445976-0
OBSOLETE 4	2.91	20	1445976-9
	2.69	18	1445976-8
	2.47	16	1445976-7
	2.25	14	1445976-6
	2.03	12	1445976-5
	1.81	10	1445976-4
OBSOLETE 4	1.59	8	1445976-3
	1.37	6	1445976-2
	1.15	4	1445976-1



1445976-1 SHOWN
SCALE 8:1



1445976-4 SHOWN
SCALE 8:1



1-1445976-9 SHOWN
SCALE 8:1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DWN D. FABIAN 06AUG2002
CHK L.BREKOSKY 05DEC2002
APVD -
PRODUCT SPEC -
APPLICATION SPEC 114-13051
WEIGHT -

tyco Electronics
Tyco Electronics Corporation
Harrisburg, PA 17105-3608

NAME
AMPMODU MICRO INTERCONNECT
HERMAPHRODITIC STRAIN RELIEF
-

DIMENSIONS: mm
TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±0.08
3 PLC ±-
4 PLC ±-
ANGLES ±1

MATERIAL - /1
FINISH - -

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	00779	C-1445976	-

CUSTOMER DRAWING | SCALE 15:1 | SHEET 1 OF 1 | REV 01