

THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION 2017
© COPYRIGHT 2017 BY -TE CONNECTIVITY ALL RIGHTS RESERVED.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	REVISED PER PCN E-17-014006	12SEP2017	SS	DM
	C	REVISED PER PCN E-19-014633	13FEB2019	AK	NS

DATE CODE: MONTH REPRESENTED BY SEQUENTIAL ALPHA CHARACTERS.
EX. A = JANUARY
YEAR IS REPRESENTED BY LAST NUMERICAL DIGIT.
EX. 6 = 2016



KEY -A- REF.





TE INTERNAL PN	DEUTSCH PN
DT06-12SA-CE13	DT06-12SA-CE13
DT06-12SB-CE13	DT06-12SB-CE13
DT06-12SC-CE13	DT06-12SC-CE13
DT06-12SD-CE13	DT06-12SD-CE13

CONTACT SIZE	MIN. INSUL O.D.	MAX. INSUL O.D.	WIRE RANGE △2 [mm^2] REF. ONLY
16	.053 [1.35]	.120 [3.05]	14-20 AWG [2.5-0.5]

△4. MATERIAL: HOUSING: PA66 GF15, SEE SHEET 2 FOR COLOR.
GROMMET: VMQ (BUNRT RED)

3. THIS PLUG MATES WITH DT04-12PX-XXXX RECEPTACLE.
(X = A,B,C,D KEY ARRANGEMENT; XXXX = ALL MODIFICATIONS).
CONSULT FACTORY FOR ALL MODIFICATIONS.

△2. FOR CONTACTS AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTICS, SEE ENVELOPE DRAWINGS 0425-015-0000.

1. SECONDARY WEDGE LOCK SOLD SEPARATELY: W12S-P012.

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES [mm]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±.025 [.64]
4 PLC ±
ANGLES ±0°30'0"

MATERIAL △4

FINISH -

DWN A.MALAGON 03AUG2006
CHK B.BYFORD 05NOV2009
APVD S.BEARD 04NOV2009
PRODUCT SPEC 108-151009
APPLICATION SPEC 114-151009
WEIGHT 20 G

TE Connectivity

NAME 12 WAY PLUG W/ SHRINK BOOT CAP AND REDUCED WIRE SEAL -CE13 MOD. DT SERIES

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	4AFU8	C-DT06-12SX-CE13	-


CUSTOMER DRAWING | SCALE 1:1 | SHEET 1 OF 2 | REV C

THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION 2017
© COPYRIGHT 2017 BY -TE CONNECTIVITY ALL RIGHTS RESERVED.


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-


PART NO.: DT06-12SA-CE13
KEY ARR. -A-
HOUSING AND CAP COLOR: GRAY




PART NO.: DT06-12SB-CE13
KEY ARR. B-
HOUSING AND CAP COLOR: BLACK



PART NO.: DT06-12SC-CE13
KEY ARR. -C-
HOUSING COLOR: GREEN
CAP COLOR: BLACK



PART NO.: DT06-12SD-CE13
KEY ARR. -D-
HOUSING COLOR: BROWN
CAP COLOR: BLACK



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES [mm]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±.025 [.64]
4 PLC ±
ANGLES ±0°30'0"

MATERIAL 4

FINISH -

DWN A.MALAGON 03AUG2006
CHK B.BYFORD 05NOV2009
APVD S.BEARD 04NOV2009
PRODUCT SPEC 108-151009
APPLICATION SPEC 0425-017-0000
WEIGHT 20 G

TE Connectivity

NAME 12 WAY PLUG W/ SHRINK BOOT CAP AND REDUCED WIRE SEAL -CE13 MOD. DT SERIES

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	4AFU8	C-DT06-12SX-CE13	-

CUSTOMER DRAWING | SCALE 1:1 | SHEET 2 OF 2 | REV C