


TABLE 1

SUB ASSEMBLY PART NO. AND CH. CODE	NO.	PART NO. AND CH. CODE	MATERIAL	COLOR	QTY.
7282-1194 ETC. ⚠2(7C82-1194, B)	①	SEE TABLE 2	⚠3 PBT	SEE TABLE 2	1
	②	7157-4080 (7B57-4080)	⚠3 PBT	⚠NATURAL	1

TABLE 2

SUB ASSEMBLY PART NO. AND CH. CODE	PART NO. AND CH. CODE	COLOR
⚠2 7282-1194, B ⚠1(7C82-1194, B)	7182-1194 ⚠1(7B82-1194)	NATURAL
7282-1194-10, B	7182-1194-10	DARK GRAY
7282-1194-30, B	7182-1194-30	BLACK
7282-1194-40, B	7182-1194-40	LIGHT GRAY
7282-1194-90, B	7182-1194-90	BLUE

注 記

⚠1. 嵌合相手品番： 7283-1194 ETC. (7C83-1194)

⚠2. 適用端子品番 2.3Ⅱ : 7114-4020, 7114-4021, 7114-4022

8.0 : 7114-6040, 7114-6041, 7114-6042

⚠2 3. ( ) 内品番はエアバック (A/B) 回路及び特別管理回路に使用する時に適用すること。

NOTES

⚠1. MATING PART NO. : 7283-1194 ETC. (7C83-1194)

⚠2. APPLICABLE TERMINAL NO. 2.3Ⅱ : 7114-4020, 7114-4021, 7114-4022

8.0 : 7114-6040, 7114-6041, 7114-6042

⚠2 3. PART NUMBERS IN PARENTHESIS SHALL BE USED FOR AIR BAG (A/B) CIRCUITS AND OTHER CIRCUITS DESIGNATED FOR SPECIAL MONITORING.

ISSUE MARK

LET	DATE	REVISION RECORD	NO.	CHKD
⚠3	06/06/07	CORRECTION OF MATERIAL	C06-Z607	H. T
⚠2	05/11/29	CHANGED PART NAME, ETC.	C05-ZE82	H. T
⚠1	96/07/12	CHANGED MATERIAL, B	C96-M264	H. K
	91/07/19	NEW	C91-L556	H. K

GENERAL TOLERANCE

	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30′	0.1
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30′	0.1
C	±0.3	±0.5	±0.8	±1.4	±2	±30′	0.15

SPECIFIED

MASS g

CUSTOMER

CUSTOMER PART NO. | CUSTOMER DWG NO.

OFFICE | TRIAL PART NO.

VENDOR

VENDOR NO.

DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE
R	NEW	91/07/19	mm	2:1	3

APPROVED	CHECKED	CHECKED	DESIGN	DRAWN
山梨	三輪	—	Y. SAWADA	M. UY 田中い
06.06.08	06.06.09		88/11/23	06/06/07

MATL. SPEC. SEE TABLE 1 | TREAT. & FIN.

NAME ⚠2 2.3Ⅱ 18P + 8.0 1P HYBRID CONNECTOR SUB ASSEMBLY MALE

PART NO. CH. CODE ⚠2 7282-1194 ETC. (7C82-1194, B)

DWG NO. 7282-1194:R | SET DWG NO.

YAZAKI CORPORATION