



REV	DESCRIPTION OF CHANGE	REVIEWED BY	ISSUE DATE
A	FIRST ISSUE	X.YAN	2021-08-01



NOTES:

1.MATERIAL:

CAGE: COPPER ALLOY,NI PLATING,THICKNESS 0.25mm

MIDDLE CAGE: STAINLESS STEEL

HEAT SINK : ALUMINUM(SURFACE TREATMENT:BLACK OXIDE


HEAT SINK CLIP: STAINLESS STEEL

2.PACKAGING: TRAY PACKAGING


3.TEMPERATURE RANGE:

OPERATING : -40°C TO +85°C

NON OPERATING : -55°C TO +105°C





TITLE SFP+ 1X2 CAGE			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd			
PART NO. SFP+ 2198230 1X2YS-CND			GENERAL TOLERANCE		UNIT:MM	SIZE: A4
APPROVE	CHECK	DRAW	.X±0.20	.X±1"	SCALE: 1:1	SHEET:1/4
QG.CHEN	SL.WANG	X.YAN	.XX±0.15	.XX±5"		
			.XXX±0.10			





PCB LAYOUT FOR SINGLE SIDE MOUNTING

TITLE SFP+ 1X2 CAGE			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd				
PART NO. SFP+ 2198230 1X2YS-CND			GENERAL TOLERANCE			UNIT:MM	SIZE: A4
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SCALE: 1:1	SHEET:2/4	REV:A
QG.CHEN	SL.WANG	X.YAN	.XX±0.15	.XX±5°			
			.XXX±0.10				





PCB LAYOUT FOR BELLY TO BELLY SIDE MOUNTING

TITLE SFP+ 1X2 CAGE			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd		
PART NO. SFP+ 2198230 1X2YS-CND			GENERAL TOLERANCE		UNIT:MM
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SCALE: 1:1
QG.CHEN	SL.WANG	X.YAN	.XX±0.15	.XX±5°	SHEET:3/4
			.XXX±0.10		REV:A



RECOMMENDED BEZEL DESIGN
SINGLE SIDED APPLICATIONS



RECOMMENDED BEZEL DESIGN
BELLY TO BELLY APPLICATIONS

TITLE SFP+ 1X2 CAGE			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd		
PART NO. SFP+ 2198230 1X2YS-CND			GENERAL TOLERANCE	UNIT:MM	SIZE: A4
APPROVE	CHECK	DRAW	.X±0.20	SCALE: 1:1	SHEET:4/4
QG.CHEN	SL.WANG	X.YAN	.XX±0.15		
			.XXX±0.10		
				REV:A	