

Specification Sheet

Part Number: TELS-13



Continuous strap and separate heads allow for any bundle diameter, eliminating waste.

Smooth strap prevents cable damage.

UV resistant materials contain an inhibitor which prolongs the life of the tie in outdoor environments.

Extended-Length Tie, POM, Black, 10-13.5" straps and 10 heads/Kit

Article Number	111-32108
----------------	-----------

Type	TELS-13
------	---------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	Extended Length Ties provide a high tensile strength strapping system consisting of a continuous strap and separate locking head making it suitable for any bundle diameter, eliminating waste. The smooth strap and specially designed heads with stainless steel pawls provide a strong grip on cables and wires without damage during vibration or in extreme environments. Spacers are available for dual bundle applications.
---------------------	--

Short Description	Extended-Length Tie, POM, Black, 10-13.5" straps and 10 heads/Kit
-------------------	---

Global Part Name	TELS-13-POM-BK
Contents of pkg/kit	10 straps (340 mm), 10 heads
Minimum Tensile Strength (Imperial)	250.0
Minimum Tensile Strength (Metric)	1115.0
Length L (Imperial)	13.5
Length L (Metric)	343.0
Fixation Method	2 piece
Identification Plate Position	none
Releasable Closure	No
Tie Closure	steel pawl
Variant	Extended Length
Width W (Imperial)	0.5
Width W (Metric)	12.7
Thickness T (Imperial)	0.06
Thickness T (Metric)	1.52
Height H (Imperial)	.49

Height H (Metric)	12.40
Material	Polyacetal (POM)
Material Shortcut	POM
Material Cable Tie	Polyacetal (POM)
Material Head	Polyacetal (POM)
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +194°F (-40°C to +90°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	10
Package Quantity (Metric)	10
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)