



© – TE Connectivity. All Rights Reserved.

| REVISIONS | | | | | |
|---|---|---|---|---|---|
| P | LTR | DESCRIPTION | DATE | DWN | APVD |
| | F1 | REV PER ECO 20-010522 | 10-16-20 | CT | RL |




| | | |
|---|---|---|
| "55" | MODULE A<br>208264-2 (SZ 22 CRIMP SOCKET CONTACT; QTY=150)<br>MODULE B<br>208265-3 (SZ 20 CRIMP PIN CONTACT; QTY=60)<br>MODULE C<br>208265-3 (SZ 20 CRIMP PIN CONTACT; QTY=24)<br>208268-3 (SZ 16 CRIMP PIN CONTACT; QTY=10) | 2221458-2 |
| "01" | MODULE A<br>208264-2 (SZ 22 CRIMP SOCKET CONTACT; QTY=150)<br>MODULE B<br>208265-3 (SZ 20 CRIMP PIN CONTACT; QTY=60)<br>MODULE C<br>208265-3 (SZ 20 CRIMP PIN CONTACT; QTY=24)<br>208268-3 (SZ 16 CRIMP PIN CONTACT; QTY=10) | 2221458-1 |
| KEYING POSITION | CONTACTS INCLUDED AND NOT INSTALLED | PART NUMBER |

1. CONNECTOR DIMENSIONS ARE PER ARINC 600 SPECIFICATION
2. DUST COVER INSTALLED FOR SHIPPING.
3. KEYING SHOWN IN POSITION "01" FOR REFERENCE ONLY.
   SEE TABLE FOR KEYING POSITION.
   FOR POSITION "00" KEYING SHIPPED UNASSEMBLED.
4. CONTACTS PACKAGED SEPARATELY AND SHIPPED WITH CONNECTOR.

| COMPONENT | MATERIAL | FINISH |
|---|---|---|
| SHELL | DIE CAST ALUMINUM PER ASTM-B-85 | ELECTROLESS NICKEL PER MIL-C-26074 |
| INSERT RETENTION PLATES | ALUMINUM ALLOY PER ASTM-B-209 | ELECTROLESS NICKEL PER MIL-C-26074 |
| SCREWS AND LOCKWASHERS | STEEL OR STAINLESS STEEL | CHROMATE OVER ZINC OR PASSIVATED |
| POLARIZING KEYS | ZINC ALLOY PER ASTM-B-86 | – |
| POLARIZING KEY RETAINING PLATE | ALUMINUM ALLOY PER ASTM-B-209 | BLUE ANODIZED PER MIL-A-8625 |
| INSERTS | THERMOSET OR THERMOPLASTIC PPS PER MIL-M-24519 | – |
| DUST COVER | CONDUCTIVE THERMOPLASTIC | – |

| | |
|---|---|
| BACC66G51F55AA | 2221458-2 |
| BACC66G51F01AA | 2221458-1 |
| CUSTOMER PART NO. | TE PART NO. |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± –
3 PLC ± –
4 PLC ± –
ANGLES ± –

MATERIAL: SEE TABLE
FINISH: SEE TABLE

| | | |
|---|---|---|
| DWN | C.C.THOMAS | 9-26-12 |
| CHK | W.BERNHART | 9-26-12 |
| APVD | W.BERNHART | 9-26-12 |
| PRODUCT SPEC | — | |
| APPLICATION SPEC | — | |
| WEIGHT | 0.000000 | |

TE Connectivity

NAME: RCPT ASSY,SIZE 2,ARINC 600 (150/60/34), RR WITH GROMMETS

| SIZE | CAGE CODE | DRAWING NO | RESTRICTED TO |
|---|---|---|---|
| A1 | 00779 | C-2221458 | — |

CUSTOMER DRAWING | SCALE 3:2 | SHEET 1 OF 1 | REV F1

4805 (1/15)