



引き出し方向
PULL DIRECTION




DETAIL U

NOTES

1. 梱包数量：3000個 / リール
NUMBER OF CONNECTORS : 3000 PCS/REEL.

2. リードテープ長さ
LEAD TAPE LENGTH





3. カバーテープの剥離強度については、IEC60286-3に準拠。
COVER TAPE PEEL FORCE IS DEFINED BY IEC 60286-3.



4. 製品詳細寸法については、図面 5051101000-SD を参照下さい。
DIMENTIONS OF PRODUCT, REFER TO 5051101000-SD.


5. 材料 MATERIAL
キャリアテープ：ポリスチレン
トップテープ：ポリエチレンテレフタレート、ポリエチレン
リール：ポリスチレン<リサイクル材を含む>
CARRIER TAPE : POLYSTYRENE
TOP TAPE : POLYETHYLENE TEREHTHALATE, POLYETHYLENE
REEL : POLYSTYRENE < RECYCLE MATERIAL CONTAINED >





THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE	CURRENT REV DESC:				molex		
mm		2:1							
GENERAL TOLERANCES (UNLESS SPECIFIED)			EC NO: 605617 DRWN: JASANUMA 2018/09/28 CHK'D: TRSUZUKI 2018/10/10 APPR: RTAKEUCHI 2018/10/10 INITIAL REVISION: DRWN: JASANUMA 2018/09/28 APPR: RTAKEUCHI 2018/10/10				0.5 FPC ZIF 2 CONT EMBT PKG		
ANGULAR TOL	±	3.0 °					PRODUCT CUSTOMER DRAWING		
4 PLACES	±	0.2					DOCUMENT NUMBER		
3 PLACES	±	0.2					5051100000-SD		
2 PLACES	±	0.2					DOC TYPE	DOC PART	REVISION
1 PLACE	±	0.25					PSD	000	A
0 PLACES	±	0.3							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER		SHEET NUMBER
				A3-SIZE	505110	SEE CHART			1 OF 3









 : PICK UP AREA



10.07	12.6	9	14.2	5051101992	19
9.57	12.1	8.5	13.7	5051101892	18
9.07	11.6	8	13.2	5051101792	17
8.57	11.1	7.5	12.7	5051101692	16
8.07	10.6	7	12.2	5051101592	15
7.57	10.1	6.5	11.7	5051101492	14
7.07	9.6	6	11.2	5051101392	13
6.57	9.1	5.5	10.7	5051101292	12
6.07	8.6	5	10.2	5051101192	11
5.57	8.1	4.5	9.7	5051101092	10
5.07	7.6	4	9.2	5051100992	9
4.57	7.1	3.5	8.7	5051100892	8
4.07	6.6	3	8.2	5051100792	7
3.57	6.1	2.5	7.7	5051100692	6
3.07	5.6	2	7.2	5051100592	5
2.57	5.1	1.5	6.7	5051100492	4
D	C	B	A	EMBOSSED PACKAGE オーダー番号 ORDER No.	Ckt

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:		molex	
DIMENSION UNITS mm	SCALE 8:1				
GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 720907		0.5 FPC ZIF 2 CONT HSG ASSY	
ANGULAR TOL $\pm 3.0^\circ$		DRWN: RAJMOK 2022/09/21		PRODUCT CUSTOMER DRAWING	
4 PLACES ± 0.2		CHK'D: YNUKANOBU 2022/09/22		DOCUMENT NUMBER	
3 PLACES ± 0.2		APPR: YNAITO 2022/09/22		5051101000-SD	
2 PLACES ± 0.2		INITIAL REVISION:		DOC TYPE	
1 PLACE ± 0.25		DRWN: JASANUMA 2018/10/01		PSD	
0 PLACES ± 0.3		APPR: RTAKEUCHI 2018/10/10		DOC PART	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING	SERIES	REVISION
			A3-SIZE	505110	B
		MATERIAL NUMBER		CUSTOMER	SHEET NUMBER
					1 OF 4



40.5	43.1	39.5	44.7	5051108091	80
35.5	38.1	34.5	39.7	5051107091	70
34.5	37.1	33.5	38.7	5051106891	68
32.5	35.1	31.5	36.7	5051106491	64
31	33.6	30	35.2	5051106191	61
30.5	33.1	29.5	34.7	5051106091	60
30	32.6	29	34.2	5051105991	59
29.5	32.1	28.5	33.7	5051105891	58
29	31.6	28	33.2	5051105791	57
28.5	31.1	27.5	32.7	5051105691	56
28	30.6	27	32.2	5051105591	55
27.5	30.1	26.5	31.7	5051105491	54
27	29.6	26	31.2	5051105391	53
26.5	29.1	25.5	30.7	5051105291	52
26	28.6	25	30.2	5051105191	51
25.5	28.1	24.5	29.7	5051105091	50
D	C	B	A	EMBOSSED PACKAGE	Ckt
				オーダー番号 ORDER No.	

25	27.6	24	29.2	5051104991	49
24.5	27.1	23.5	28.7	5051104891	48
24	26.6	23	28.2	5051104791	47
23.5	26.1	22.5	27.7	5051104691	46
23	25.6	22	27.2	5051104591	45
22.5	25.1	21.5	26.7	5051104491	44
22	24.6	21	26.2	5051104391	43
21.5	24.1	20.5	25.7	5051104291	42
21	23.6	20	25.2	5051104191	41
20.5	23.1	19.5	24.7	5051104091	40
D	C	B	A	EMBOSSED PACKAGE	Ckt
				オーダー番号 ORDER No.	

20	22.6	19	24.2	5051103991	39
19.5	22.1	18.5	23.7	5051103891	38
19	21.6	18	23.2	5051103791	37
18.5	21.1	17.5	22.7	5051103691	36
18	20.6	17	22.2	5051103591	35
17.5	20.1	16.5	21.7	5051103491	34
17	19.6	16	21.2	5051103391	33
16.5	19.1	15.5	20.7	5051103291	32
16	18.6	15	20.2	5051103191	31
15.5	18.1	14.5	19.7	5051103091	30
D	C	B	A	EMBOSSED PACKAGE	Ckt
				オーダー番号 ORDER No.	

15	17.6	14	19.2	5051102991	29
14.5	17.1	13.5	18.7	5051102891	28
14	16.6	13	18.2	5051102791	27
13.5	16.1	12.5	17.7	5051102691	26
13	15.6	12	17.2	5051102591	25
12.5	15.1	11.5	16.7	5051102491	24
12	14.6	11	16.2	5051102391	23
11.5	14.1	10.5	15.7	5051102291	22
11	13.6	10	15.2	5051102191	21
10.5	13.1	9.5	14.7	5051102091	20
D	C	B	A	EMBOSSED PACKAGE	Ckt
				オーダー番号 ORDER No.	

