THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION – –, .
© COPYRIGHT – By – ALL RIGHTS RESERVED.

LOC	DIST
FT	0


REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	REVISED PER ECO–11–005027	11MAR11	RK	HMR


MATERIALS:
HOUSING: POLYAMIDE, UL94V–0.
TERMINALS: COPPER ALLOY, TIN PLATED.
SCREWS: STEEL, ZINC PLATED.

ELECTRICAL:
RATING: 20A 150V(300 LIMITED RATING)
UL & CSA.

MECHANICAL:
WIRE RANGE: 14–22 AWG
MAXIMUM TIGHTENING TORQUE: 7 IN–LB
RUNNING TORQUE: 0.5–3.5 IN–LB.







DIM "A"	DIM "B"	NO OF POS	CATALOG NUMBER	PART NUMBER
9.811	9.425	28	4PCR–28–008	2–1546940–6
9.486	9.100	27	4PCR–27–008	2–1546940–5
9.161	8.775	26	4PCR–26–008	2–1546940–4
8.836	8.450	25	4PCR–25–008	2–1546940–3
8.511	8.125	24	4PCR–24–008	2–1546940–2
8.186	7.800	23	4PCR–23–008	2–1546940–1
7.861	7.475	22	4PCR–22–008	2–1546940–0
7.536	7.150	21	4PCR–21–008	1–1546940–9
7.211	6.825	20	4PCR–20–008	1–1546940–8
6.886	6.500	19	4PCR–19–008	1–1546940–7
6.561	6.175	18	4PCR–18–008	1–1546940–6
6.236	5.850	17	4PCR–17–008	1–1546940–5
5.911	5.525	16	4PCR–16–008	1–1546940–4
5.586	5.200	15	4PCR–15–008	1–1546940–3
5.261	4.875	14	4PCR–14–008	1–1546940–2
4.936	4.550	13	4PCR–13–008	1–1546940–1
4.611	4.225	12	4PCR–12–008	1–1546940–0
4.286	3.900	11	4PCR–11–008	1546940–9
3.961	3.575	10	4PCR–10–008	1546940–8
3.636	3.250	9	4PCR–09–008	1546940–7
3.311	2.925	8	4PCR–08–008	1546940–6
2.986	2.600	7	4PCR–07–008	1546940–5
2.661	2.275	6	4PCR–06–008	1546940–4
2.336	1.950	5	4PCR–05–008	1546940–3
2.011	1.625	4	4PCR–04–008	2–1546158–1
1.686	1.300	3	4PCR–03–008	1546940–2
1.361	.975	2	4PCR–02–008	1546940–1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± .01
3 PLC ± .005
4 PLC ± –
ANGLES ± 1°

MATERIAL –
FINISH –

DWN	S SCHLEGEL	10/20/06
CHK	S. YODER	10/20/06
APVD	S. YODER	10/20/06
PRODUCT SPEC	–	
APPLICATION SPEC	–	
WEIGHT	–	

TE Connectivity

NAME: 4PCR–XX–008 ASSEMBLY

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C–2–1546158–1	–

CUSTOMER DRAWING

SCALE	SHEET	REV
NTS	1 OF 1	B1