

TABLE 1

SUB ASSEMBLY PART NO. AND CH. CODE	NO.	PART NO. AND CH. CODE	MATERIAL	COLOR	QTY.
7283-1160 ETC.	①	SEE TABLE 2	⚠HPA	SEE TABLE 2	1
	②	7157-4033	⚠HPA	NATURAL	1

⚠TABLE 2

SUB ASSEMBLY PART NO. AND CH. CODE	PART NO. AND CH. CODE	COLOR
7283-1160-Ⓐ	7183-1160	NATURAL
7283-1160-10-Ⓐ	7183-1160-10	DARK GRAY
7283-1160-30-Ⓐ	7183-1160-30	BLACK
7283-1160-40-Ⓐ	7183-1160-40	LIGHT GRAY
7283-1160-90-Ⓐ	7183-1160-90	BLUE





SEC. A-A

NOTES

1. MATING PART NO. : 7282-1160 ETC.
2. APPLICABLE TERMINAL NO. :7116-4020 ETC.

注記

3. 嵌合相手品番 : 7282-1160 ETC.
2. 適用端子品番 : 7116-4020 ETC.

ISSUE MARK

⚠	98. 12. 23	ELIMINATED COLOR NO.	C98-N184	T. M
⚠	97. 06. 19	ADDED PART NO. & CHANGED MATERIAL Ⓐ	C97-N141	M. T
	90. 11. 10	NEW	C90-M213	M. H
LET	DATE	REVISION RECORD	NO.	CHKD

GENERAL TOLERANCE

	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT
A	±0. 15	±0. 2	±0. 3	±0. 5	±0. 75	±30′	0. 1
B	±0. 2	±0. 3	±0. 55	±0. 95	±1. 4	±30′	0. 1
(C)	±0. 3	±0. 5	±0. 8	±1. 4	±2	±30′	0. 15

SPECIFIED — MASS g

CUSTOMER						
CUSTOMER PART NO.		CUSTOMER DWG NO.				
OFFICE		TRIAL PART NO.				
VENDOR						
VENDOR NO.						
DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE	
R	NEW	90. 11. 10	mm	2/1	3	
APPROVED	CHECKED	CHECKED	DESIGN	DRAWN		
加藤	川梨	鶴	Y. OHTA	KANAZAWA 杉山		
99. 1. 15	99. 1. 14	99.01.07	89. 05. 22	98. 12. 23		

MATL. SPEC.	SEE TABLE 1
TREAT. & FIN.	
NAME	090Ⅱ 16P CONNECTOR SUB ASSEMBLY FEMALE
PART NO. CH. CODE	7283-1160 ETC.
DWG NO.	7283-1160:R
SET DWG NO.	

YAZAKI CORPORATION