






技术指标:

1. 温度范围: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
2. 额定电压: 250V AC, DC.
3. 耐电压: 1500V AC/minute.
4. 接触电阻: $\leq 20\text{m}\Omega$.
5. 绝缘电阻: $\geq 1000\text{M}\Omega$.
6. 额定电流: 5A AC, DC.

材料:

1. 塑胶: PA66 黑色



型号	CKT	A	B
XY-MX3.0-02A41-G	2*1	0.00	5.20
XY-MX3.0-04A41-G	2*2	3.00	8.20
XY-MX3.0-06A41-G	2*3	6.00	11.20
XY-MX3.0-08A41-G	2*4	9.00	14.20
XY-MX3.0-10A41-G	2*5	12.00	17.20
XY-MX3.0-12A41-G	2*6	15.00	20.20
XY-MX3.0-14A41-G	2*7	18.00	23.20
XY-MX3.0-16A41-G	2*8	21.00	26.20
XY-MX3.0-18A41-G	2*9	24.00	29.20
XY-MX3.0-20A41-G	2*10	27.00	32.20
XY-MX3.0-22A41-G	2*11	30.00	35.20
XY-MX3.0-24A41-G	2*12	33.00	38.20

族壳型号	CKT	匹配端子
XY-MX3.0-02A41-G	2*1	XY-MX3.0-31-G
XY-MX3.0-04A41-G	2*2	
XY-MX3.0-06A41-G	2*3	
XY-MX3.0-08A41-G	2*4	
XY-MX3.0-10A41-G	2*5	
XY-MX3.0-12A41-G	2*6	
XY-MX3.0-14A41-G	2*7	XY-MX3.0-31-DG
XY-MX3.0-16A41-G	2*8	
XY-MX3.0-18A41-G	2*9	
XY-MX3.0-20A41-G	2*10	
XY-MX3.0-22A41-G	2*11	
XY-MX3.0-24A41-G	2*12	

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	TITLE: MX3.0MM HOUSING		
X.X $\pm$ 0.30	X.* $\pm$ 5°	Alex	DWG NO. XY-MX3.0-NA41-G		
X.XX $\pm$ 0.25	X.X° $\pm$ 1°	Jack	PROJ.  CUSTOMER DRAWING		
X.XXX $\pm$ 0.15		Can	SIZE A4	SCALE 1:1	SHEET 1/1 REV. A