



NOTE:
 Operating Force:
 lever portion 70 ± 40 gf
 Push portion 200 ± 40 gf

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑥	Terminal	—	8	Brass	Plating silver	—
⑤	Contact	—	1	F.Ag/Brass	Plating silver	—
④	Base	—	1	PA46	Black	—
③	Spring	—	1	SUS	Natural	—
②	Cover	—	1	SUS	Natural	—
①	Keystroke	—	1	PA46	Black	—

Circuit Diagram
 P.C.B Mounting
 Pattern Dimension

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.																												
	A		NEW																															
<table border="1"> <thead> <tr> <th>APPROVALS</th> <th>DATE</th> <th>TITLE:</th> <th>PART NO.</th> <th>SCALE:</th> <th>PROJ.</th> <th>SHEET</th> </tr> </thead> <tbody> <tr> <td>DRAWN J.X.Zhang</td> <td>2013/8/8</td> <td>ELECTRONICS CO.,LTD</td> <td>K1-1501SA-01</td> <td>1:1</td> <td>PROJ. 1501SA-01</td> <td>1 OF 1</td> </tr> <tr> <td>CHECKED</td> <td></td> <td>MULTIFUNCTIONAL SWITCHS</td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>APPROVALS</td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> </tbody> </table>							APPROVALS	DATE	TITLE:	PART NO.	SCALE:	PROJ.	SHEET	DRAWN J.X.Zhang	2013/8/8	ELECTRONICS CO.,LTD	K1-1501SA-01	1:1	PROJ. 1501SA-01	1 OF 1	CHECKED		MULTIFUNCTIONAL SWITCHS					APPROVALS						
APPROVALS	DATE	TITLE:	PART NO.	SCALE:	PROJ.	SHEET																												
DRAWN J.X.Zhang	2013/8/8	ELECTRONICS CO.,LTD	K1-1501SA-01	1:1	PROJ. 1501SA-01	1 OF 1																												
CHECKED		MULTIFUNCTIONAL SWITCHS																																
APPROVALS																																		
TOLERANCES ARE		30~125 ± 0.30	±0.30	ANGLE	±2°	DRAWING NO.																												
		10~30 ±0.20	±0.20																															
		5~10 ±0.15	±0.15																															
		~5 ±0.10	±0.10																															