












RECOMMENDED PCB(CONNECTOR SIDE VIEW)
THICKNESS=1.6 TO 2.4 MM




ONLY FOR CKT 6, 10, 14
OTHER DIMENSIONS REFER TO LEFT VIEWS.



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex			
mm		5:1									
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 749038 DRWN: GLLI 2023/05/10 CHK'D: XQZHANG 2023/05/25 APPR: XQZHANG 2023/05/25							
ANGULAR TOL ± 3.0 °											
4 PLACES		±		PRODUCT CUSTOMER DRAWING							
3 PLACES		± 0.1									
2 PLACES		± 0.2		DOCUMENT NUMBER SD-105310-100							
1 PLACE		± 0.3									
0 PLACES		±		DOC TYPE		DOC PART		REVISION			
INITIAL REVISION:				2014/03/21		PSD		000		H1	
DRWN: GLLI				2015/04/08		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
APPR: AYIN								GENERAL MARKET		1 OF 5	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES			
						A3-SIZE		105310			




KEY A




KEY A

BLACK




KEY B



KEY B


NATURAL

COLOR OPTION

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex			
mm		5:1									
GENERAL TOLERANCES (UNLESS SPECIFIED)				HEADER OF NANO-FIT, D/R, KINK, VERTICAL POWER CONNECTOR							
ANGULAR TOL ± 3.0 °											
4 PLACES ±				EC NO: 749038 DRWN: GLLI 2023/05/10 CHK'D: XQZHANG 2023/05/25 APPR: XQZHANG 2023/05/25							
3 PLACES ± 0.1											
2 PLACES ± 0.2											
1 PLACE ± 0.3				PRODUCT CUSTOMER DRAWING							
0 PLACES ±											
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
				SD-105310-100		PSD		000		H1	
THIRD ANGLE PROJECTION				DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER	
				A3-SIZE		105310				GENERAL MARKET	
										SHEET NUMBER	
										2 OF 5	

DOCUMENT STATUS	P1	RELEASE DATE	2023/05/25	00:11:27
-----------------	----	--------------	------------	----------

FORMAT: master-b-prod-A3
REVISION: J1
DATE: 2021/05/01

10		9		8		7		6		5		4		3		2		1					
PART NUMBER		DIM 'A'	DIM 'B'	CKT SIZE	PLATING	LUBE	 105310- * * * * CIRCUIT SIZE PLATING OPTION 1 - TIN 2 - GOLD 0.38 3 - GOLD 0.76 4 - GOLD AND LUBE 5 - GOLD 0.025 COLOR OPTION 1 - BLACK 2 - NATURAL										PART NUMBER		DIM 'A'	DIM 'B'	CKT SIZE	PLATING	LUBE
105310-1104		5.94	2.50	4	TIN												105310-2104		5.94	2.50	4	TIN	
105310-1106		8.44	5.00	6													105310-2106		8.44	5.00	6		
105310-1108		10.94	7.50	8													105310-2108		10.94	7.50	8		
105310-1110		13.44	10.00	10													105310-2110		13.44	10.00	10		
105310-1112		15.94	12.50	12													105310-2112		15.94	12.50	12		
105310-1114		18.44	15.00	14	GOLD 0.38	NO											105310-2114		18.44	15.00	14	GOLD 0.38	NO
105310-1116		20.94	17.50	16													105310-2116		20.94	17.50	16		
105310-1204		5.94	2.50	4													105310-2204		5.94	2.50	4		
105310-1206		8.44	5.00	6													105310-2206		8.44	5.00	6		
105310-1208		10.94	7.50	8													105310-2208		10.94	7.50	8		
105310-1210		13.44	10.00	10	GOLD 0.76												105310-2210		13.44	10.00	10	GOLD 0.76	
105310-1212		15.94	12.50	12													105310-2212		15.94	12.50	12		
105310-1214		18.44	15.00	14													105310-2214		18.44	15.00	14		
105310-1216		20.94	17.50	16													105310-2216		20.94	17.50	16		
105310-1304		5.94	2.50	4													105310-2304		5.94	2.50	4		
105310-1306		8.44	5.00	6	GOLD 0.76												105310-2306		8.44	5.00	6	GOLD 0.76	
105310-1308		10.94	7.50	8													105310-2308		10.94	7.50	8		
105310-1310		13.44	10.00	10													105310-2310		13.44	10.00	10		
105310-1312		15.94	12.50	12													105310-2312		15.94	12.50	12		
105310-1314		18.44	15.00	14			105310-2314		18.44	15.00	14												
105310-1316		20.94	17.50	16	GOLD 0.76	YES	105310-2316		20.94	17.50	16	GOLD 0.76	YES										
105310-1404		5.94	2.50	4			105310-2404		5.94	2.50	4												
105310-1406		8.44	5.00	6			105310-2406		8.44	5.00	6												
105310-1408		10.94	7.50	8			105310-2408		10.94	7.50	8												
105310-1410		13.44	10.00	10			105310-2410		13.44	10.00	10												
105310-1412		15.94	12.50	12	GOLD 0.76	YES	105310-2412		15.94	12.50	12	GOLD 0.76	YES										
105310-1414		18.44	15.00	14			105310-2414		18.44	15.00	14												
105310-1416		20.94	17.50	16			105310-2416		20.94	17.50	16												
COLOR: BLACK							COLOR: NATURAL																
PART NUMBER		DIM 'A'	DIM 'B'	CKT SIZE	PLATING	LUBE	PART NUMBER		DIM 'A'	DIM 'B'	CKT SIZE	PLATING	LUBE										
105310-1504		5.94	2.50	4	GOLD 0.025	NO	105310-2504		5.94	2.50	4	GOLD 0.025	NO										
105310-1506		8.44	5.00	6			105310-2506		8.44	5.00	6												
105310-1508		10.94	7.50	8			105310-2508		10.94	7.50	8												
105310-1510		13.44	10.00	10			105310-2510		13.44	10.00	10												
105310-1512		15.94	12.50	12			105310-2512		15.94	12.50	12												
105310-1514		18.44	15.00	14	GOLD 0.025	NO	105310-2514		18.44	15.00	14	GOLD 0.025	NO										
105310-1516		20.94	17.50	16			105310-2516		20.94	17.50	16												
COLOR: BLACK							COLOR: NATURAL																
DOCUMENT STATUS		P1	RELEASE DATE		2023/05/25 00:11:27		PART NUMBER		DIM 'A'	DIM 'B'	CKT SIZE	PLATING	LUBE										
105310-1504		5.94	2.50	4	GOLD 0.025	NO	105310-2504		5.94	2.50	4	GOLD 0.025	NO										
105310-1506		8.44	5.00	6			105310-2506		8.44	5.00	6												
105310-1508		10.94	7.50	8			105310-2508		10.94	7.50	8												
105310-1510		13.44	10.00	10			105310-2510		13.44	10.00	10												
105310-1512		15.94	12.50	12			105310-2512		15.94	12.50	12												

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS

mm

SCALE

5:1

GENERAL TOLERANCES (UNLESS SPECIFIED)

ANGULAR TOL ± 3.0 °

4 PLACES ±

3 PLACES ± 0.1

2 PLACES ± 0.2

1 PLACE ± 0.3

0 PLACES ±

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

THIRD ANGLE PROJECTION

DRAWING A3-SIZE

SERIES 105310

CURRENT REV DESC:

EC NO: 749038

DRWN: GLLI

CHK'D: XQZHANG

APPR: XQZHANG

INITIAL REVISION:

DRWN: GLLI

APPR: AYIN

2023/05/10

2023/05/25

2023/05/25

2014/03/21

2015/04/08

DOCUMENT NUMBER

SD-105310-100

DOCUMENT TYPE

PSD

DOCUMENT PART

000

DOCUMENT REVISION

H1

MATERIAL NUMBER

CUSTOMER

SHEET NUMBER
















GENERAL MARKET

3 OF 5

HEADER OF NANO-FIT, D/R, KINK, VERTICAL POWER CONNECTOR

PRODUCT CUSTOMER DRAWING

molex

	10	9	8	7	6	5	4	3	2	1	
F			4 CKT	6 CKT	8 CKT	10 CKT					F
	BLACK										
E	NATURAL										E
		12 CKT	14 CKT	16 CKT							
D	BLACK										D
C	NATURAL										C
B											B
A											A
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION DIMENSION UNITS mm SCALE 3:1 GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± 3.0 ° 4 PLACES ± 3 PLACES ± 0.1 2 PLACES ± 0.2 1 PLACE ± 0.3 0 PLACES ± DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS THIRD ANGLE PROJECTION  DRAWING A3-SIZE SERIES 105310 CURRENT REV DESC: EC NO: 749038 DRWN: GLLI CHK'D: XQZHANG APPR: XQZHANG INITIAL REVISION: DRWN: GLLI APPR: AYIN 2023/05/10 2023/05/25 2023/05/25 2014/03/21 2015/04/08 DOCUMENT NUMBER SD-105310-100 DOC TYPE PSD DOC PART 000 REVISION H1 MATERIAL NUMBER CUSTOMER GENERAL MARKET SHEET NUMBER 4 OF 5 DOCUMENT STATUS P1 RELEASE DATE 2023/05/25 00:11:27											
	9	8	7	6	5	4	3	2	1		

NOTES FOR ALL PARTS

- 1> MATERIAL:
HOUSING: LCP, UL 94V-0; TERMINAL: BRASS.

2> PLATING FINISHED:
TERMINAL:
CONTACT AREA: a. REFLOWED MATTE TIN 1.5MICRONS MIN;
b. GOLD 0.38 MICRONS MIN;
c. GOLD 0.76 MICRONS MIN.
d. GOLD 0.025 MICRONS MIN.
SOLDER AREA: TIN 1.5 MICRONS MIN, UNDER PLATING NICKEL 1.25 MICRONS MIN.
SOLDER CLIP: TIN 2.5 MICRONS MIN, UNDER PLATING NICKEL 1.25 MICRONS MIN.


3> PRODUCT SPECIFICATION: PS-105300-100.
- 4> PACKAGE: TRAY, PK-105309-100.

5> ALL COMPONENTS AND PRODUCT COMPLIANT TO RoHS DIRECTIVE 2011/65/EU AND ELV DIRECTIVE 2000/53/EC.

6> PRODUCT MATE WITH SERIES OF 105308(RECEPTACLE), 105300(CRIMP TERMINAL).

7> PARTS CONFORM TO CLASS 'B'REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.

8> DISCOLORATION IN THE BANDOLIER PIN CARRIER AREA OF THE PIN IS INHERENT TO THE PLATING PROCESS AND IS DUE TO THE MASKING DEFECT OF THE CARRIER, THIS DISCOLORATION IS IN A NON-FUNCTION AREA OF THE PIN AND WILL NOT AFFECT THE PERFORMANCE OF THE HEADER ASSEMBLY.



IF ANY NUMBER MARK APPEARS ON THIS SURFACE, PLEASE DISREGARD IT, IT IS NO ANY FUCTION AND NO ANY RELATION TO PIN NUMBER, IT IS JUST FOR MOLDING IDENDIFICATION.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex					
mm		1:1										
GENERAL TOLERANCES (UNLESS SPECIFIED)							EC NO: 749038 DRWN: GLLI 2023/05/10 CHK'D: XQZHANG 2023/05/25 APPR: XQZHANG 2023/05/25			HEADER OF NANO-FIT, D/R, KINK, VERTICAL POWER CONNECTOR		
ANGULAR TOL ± 3.0 °				PRODUCT CUSTOMER DRAWING								
4 PLACES		±								DOCUMENT NUMBER SD-105310-100 DOC TYPE PSD DOC PART 000 REVISION H1		
3 PLACES		± 0.1										
2 PLACES		± 0.2										
1 PLACE		± 0.3										
0 PLACES		±		INITIAL REVISION: DRWN: GLLI 2014/03/21 APPR: AYIN 2015/04/08			MATERIAL NUMBER GENERAL MARKET CUSTOMER GENERAL MARKET SHEET NUMBER 5 OF 5					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS												
THIRD ANGLE PROJECTION			DRAWING		SERIES							
			A3-SIZE		105310							