ATGBICS

ATGBICS Universally Coded MSA Compliant Transceiver CWDM SFP+ 10GBase (40km, SMF, LC 1610nm, DOM)

Brand : ATGBICS

Product code: CWDM-SFP-10G-1610-40-MSA-AT

Product name : Universally Coded MSA Compliant Transceiver CWDM SFP+ 10GBase (40km, SMF, LC 1610nm, DOM)



ATGBICS Universally Coded MSA Compliant Transceiver CWDM SFP+ 10GBase (40km, SMF, LC 1610nm, DOM)

ATGBICS Universally Coded MSA Compliant Transceiver CWDM SFP+ 10GBase (40km, SMF, LC 1610nm, DOM):

ATGBICS Universally Coded MSA Network Transceivers are specifically designed for use in 'open standard' platforms. Unlike some OEMs such as Cisco and HP, other network equipment manufacturers do not have specific firmware coding requirements for compatibility with their brand of networking equipment. This form of 'open coding' or 'generic coding' network infrastructure supports versatile purchasing options of network transceivers. Our plug and play Universally Coded Transceivers are also ideal for clients building their own bespoke infrastructure. Our product meets all Multi-Source Agreement (MSA) standards for this form factor and are uniquely serialised for full date code and BOM traceability. We proudly offer a compatibility guarantee and lifetime replacement warranty

Performance	
SFP transceiver type *	Fiber optic
Maximum data transfer rate *	10000 Mbit/s
Interface type *	SFP+
Single-mode fiber (SMF) supported	✓
Multi-mode fiber (MMF) supported	✗
Fiber optic connector	LC
SFP transceiver standard	CWDM
Maximum transfer distance	40000 m
Wavelength	1610 nm
Coarse Wavelength Division Multiplexing (CWDM)	✓
Ethernet LAN	✓
Ethernet interface type	10 Gigabit Ethernet
Digital Diagnostics Monitoring (DDM)	✓

Features	
Product colour	Silver
Housing material	Metal
Plug and Play	✓
Hot-swap	✓
Easy to install	✓
Country of origin	United Kingdom
Brand compatibility	MSA Compliant

Features	
Certification	CE, FCC, RoHS

Power	
Input voltage	3.3 V
Maximum voltage	3.5 V
Power consumption (typical)	1 W

Operational conditions	
Maximum operating temperature	70 °C
Operating temperature (T-T)	0 - 70 °C
Storage temperature (T-T)	-40 - 85 °C
Operating relative humidity (H-H)	0 - 95%
Storage relative humidity (H-H)	0 - 95%

Weight & dimensions	
Width	13.4 mm
Depth	56.5 mm
Height	8.5 mm
Weight	20 g

Packaging data	
Number of products included	1 pc(s)
Package type	Blister

Technical details	
Sustainability compliance	✓
Sustainability certificates	RoHS, Federal Communications Commission (FCC), CE, REACH
Doesn't contain	Lead



5056468774576

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 26-JAN-2024. Prints or copies of Information are only valid on the printed Publication date