

Features

- Low on-resistance
- High-speed switching
- Drive circuits can be simple
- Parallel use is easy

Typical Applications


- Switching application

Shipping Quantity

- 3000pcs / Tape & Reel



Circuit Diagram



N-MOS

Absolute Maximum Ratings (T_{amb}=25°C unless otherwise specified)

Parameter	Symbol	Value	Unit
Drain-to-Source Voltage	V _{DSS}	100	V
Gate-to-Source Voltage	V _{GSS}	±20	V
Continuous Drain Current	I _D	170	mA
Pulsed Drain Current *3	I _{DM}	680	mA



Thermal Characteristics







Parameter		Symbol	Value	Unit
Power Dissipation	SOT-23	P_D	0.35	W
Thermal Resistance Junction-to-Air	SOT-23	$R_{\theta JA}$	357	$^{\circ}C/W$
Operating Junction Temperature Range		T_J	-55 to +150	$^{\circ}C$
Storage Temperature Range		T_{STG}	-55 to +150	$^{\circ}C$

Electrical Characteristics ($T_A=25^{\circ}C$ unless otherwise specified)

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
Static Characteristics						
V_{DSS}	Drain-Source Breakdown Voltage	$V_{GS} = 0V, I_D = 250\mu A$	100	-	-	V
I_{DSS}	Zero Gate Voltage Drain Current	$V_{DS} = 100V, V_{GS} = 0V$	-	-	1	μA
		$V_{DS} = 20V, V_{GS} = 0V$	-	-	10	nA
I_{GSS}	Gate-Body Leakage Current	$V_{GS} = \pm 20V, V_{DS} = 0V$	-	-	± 1	μA
On Characteristics						
$R_{DS(ON)}$	Static Drain-Source On-resistance *1	$V_{GS} = 10V, I_D = 0.17A$	-	3.0	6	Ω
		$V_{GS} = 4.5V, I_D = 0.17A$	-	3.5	10	
$V_{GS(TH)}$	Gate Threshold Voltage	$V_{DS} = V_{GS}, I_D = 250\mu A$	1	1.9	2.8	V
Dynamic Characteristics						
C_{iss}	Input Capacitance	$V_{GS} = 0V$	-	43	-	pF
C_{oss}	Output Capacitance	$V_{DS} = 20V$	-	15	-	
C_{rss}	Reverse Transfer Capacitance	$f = 1.0MHz$	-	2.8	-	
Switching Characteristics *2						
$t_{d(on)}$	Turn-on Delay Time	$V_{DD} = 30V, I_D = 0.28A$ $V_{GS} = 10V, R_G = 50\Omega$	-	-	8	ns
t_r	Turn-on Rise Time		-	-	8	
$t_{d(off)}$	Turn-Off Delay Time		-	-	13	
t_f	Turn-Off Fall Time		-	-	16	
Source-Drain Diode Characteristics						
V_{SD}	Diode Forward Voltage *1	$I_S = 0.3A, V_{GS} = 0V$	-	0.85	1.3	V




Typical Performance Characteristics (T_A=25°C unless otherwise Specified)





Outline Drawing - SOT23



SOT-23		
Dimension	Min.	Max.
A	2.70	3.10
B	1.10	1.50
C	0.90	1.10
D	0.30	0.50
E	0.35	0.48
G	1.80	2.00
H	0.02	0.10
J	0.05	0.15
K	2.20	2.60

Land Pattern - SOT23

