








技术指标:

1. 额定电流: 0.5A
2. 温度范围: -40~85℃
3. 额定电压: 50V, AC/DC (等效)
4. 接触电阻: $\leq 0.03\Omega$
5. 绝缘电阻: $\geq 500M\Omega$

序号	品名	材质
1	端子	磷青铜/表面镀锡
2	焊片	黄铜/表面镀锡
3	基座	LCP UL94V-0 本色
4	锁条	LCP UL94V-0 黑色



Part No	Pin	A	B	C
AFPC0502-4PH2.0	4	1.50	2.60	6.40
AFPC0502-5PH2.0	5	2.00	3.10	6.90
AFPC0502-6PH2.0	6	2.50	3.60	7.40
AFPC0502-7PH2.0	7	3.00	4.10	7.90
AFPC0502-8PH2.0	8	3.50	4.60	8.40
AFPC0502-9PH2.0	9	4.00	5.10	8.90
AFPC0502-10PH2.0	10	4.50	5.60	9.40
AFPC0502-11PH2.0	11	5.00	6.10	9.90
AFPC0502-12PH2.0	12	5.50	6.60	10.40
AFPC0502-13PH2.0	13	6.00	7.10	10.90
AFPC0502-14PH2.0	14	6.50	7.60	11.40
AFPC0502-15PH2.0	15	7.00	8.10	11.90
.....		...		
AFPC0502-60PH2.0	60	(61-1)*0.5	(61+1)*0.5+0.1	(61+7)*0.5+0.9



TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.±0.15	±1°	PART NO.	TITLE:	
X.X±0.10		AFPC0502-NPH2.0	0.5-B 差(H:2.0)	
X.XX±0.05		DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olvia		SCALE
MATERILA	---	APPD: Ava		SHEET
FINISH	---		N:A	1/1