6609068-4 ✔ ACTIVE

Corcom | Corcom AYC


TE Internal #: 6609068-4

25A Current Rating, Terminal Block Input, Terminal Block Output, WYE (4 wire + ground), Operating Voltage 480 VAC, Corcom AYC, 3-Phase Filters

View on TE.com >

EMI & EMC Solutions > EMI Filters > Power Line Filters > 3-Phase Filters > Corcom 3-Phase Power Line Filters, AYC Series







Current Rating: **25 A**

Input Termination Type: **Terminal Block**

Output Termination Type: **Terminal Block**

Wiring Configuration: **WYE (4 wire + ground)**

Operating Voltage: **480 VAC**

All Corcom 3-Phase Power Line Filters, AYC Series (1)

Features

Product Type Features

Filtering Requirements	Filtered
Input Termination Type	Terminal Block
Output Termination Type	Terminal Block

Configuration Features

Wiring Configuration	WYE (4 wire + ground)

Electrical Characteristics

Leakage Current (Max) (250VAC, 50Hz)	118 mA
Current Rating	25 A
Operating Voltage	480 VAC

Mechanical Attachment

Product Mount Type	Chassis

Usage Conditions

Operating Temperature Range	-10 – 40 °C

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # CAT-C8114-A11
EMI Filter Accessories, Corcom A Series




TE Part # CAT-C8114-AY61
3 Phase Filters, Corcom AYO Series

Also in the Series | Corcom AYC



3-Phase Filters(1)

Customers Also Bought



TE Part #T4071017041-001
M8.FMLE.PNLREAR.4POS.STR WIRE




TE Part #770251-3
UMNL II SOK PTPPHBZ LP 20-14



TE Part #640900-1
05P UMNL PIN HDR ASSY 94VO



TE Part #350789-1
03P UMNL PIN HDR ASSY 94VO



TE Part #1-770174-1
04P MINI UMNL ASSY VO SNAU LF



TE Part #770027-1
06P UMNLII IN-LINE CAP HSG KIT



TE Part #770020-1
06P UMNLII IN-LNE PLUG HSG KIT



TE Part #1-100103-0
10P.A/L.STRAIN REL.



TE Part #8-1393483-7
V42254A2115B209=SUB D FEDERLEI

Documents

CAD Files

Customer View Model
ENG_CVM_CVM_6609068-4_P.2d_dxf.zip
English

Customer View Model
ENG_CVM_CVM_6609068-4_P.3d_igs.zip
English

Customer View Model
ENG_CVM_CVM_6609068-4_P.3d_stp.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

1654001_Corcom_Product_Guide_AYC_Series

English

Corcom Combined Selector Charts

English

1-1654250-1_CORCOM_EMI_RFI_QRG

English

Agency Approvals

UL Report

English