







REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



SPECIFICATIONS

Current Rating: 1.5 Amps
 Insulation Resistance: 1000M Ω Min
 Contact Resistance: 20m Ω Max
 Withstanding Voltage: AC 500V
 Operation Temperature: -40° to +105°
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester (UL 94V-0)
 Contact Plating: Gold Flash
 Max. Processing Temp: 240°C for 30-60 seconds (260°C for 5 seconds)



RECOMMEND P.C.B LAYOUT
 PCB TOLERANCE: ±0.05 (TOP VIEW)

P/N	PIN	DIM.A	DIM.B
B200M05-0B2P51R-H43C65	2*1	0.00	2.00
B200M05-0B4P51R-H43C65	2*2	2.00	4.00
B200M05-0B6P51R-H43C65	2*3	4.00	6.00
B200M05-0B8P51R-H43C65	2*4	6.00	8.00
B200M05-0B10P51R-H43C65	2*5	8.00	10.00
B200M05-0B12P51R-H43C65	2*6	10.00	12.00
B200M05-0B14P51R-H43C65	2*7	12.00	14.00
B200M05-0B16P51R-H43C65	2*8	14.00	16.00
B200M05-0B18P51R-H43C65	2*9	16.00	18.00
.....
B200M05-0B80P51R-H43C65	2*40	(40-1)x2.0	(40)x2.0

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.X ±0.30	X.° ±5°	PART NO.	TITLE: 2.0FH H4.3 2xnPin	
.XX ±0.20	X.X° ±1°	B200M05-0BXP51R-H43C65	SMT W4.5 U型 PC6.5 PB4.6 6T	
.XXX ±0.10	X.XX° ±0.5°	DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olivia		
MATERILA	---	APPD: Ava	SCALE	SHEET
FINISH	---		N:A	1/1