

1		2			3			4		5		6		7		8																																																	
linear dimension (Tolerances Standard GB/T 14486-2008)										—	\square	\perp	版本 Version	描述 Description	设计 Design	批准 Approved	日期 Date																																																
A	variable range	to	over	over	over	over	over	over	over	over	to	to	to	to	to	to	to																																																
		6	6	10	30	60	100	160	to	10	100	to	to	to	to	to	to	to																																															
tolerance		± 0.20	± 0.30	± 0.50	± 0.70	± 1.00	± 1.30	± 1.60	0.10	0.30	0.60																																																						
<table border="1"> <tr> <th colspan="2">材质及电镀 MATERIAL</th> </tr> <tr> <td>螺丝 Screws</td> <td>M2.5, 钢, 镀锌 M2.5, Steel, Zn plated</td> </tr> <tr> <td>夹片 Clamp</td> <td>铜合金, 镀镍 Copper alloy, Ni plated</td> </tr> <tr> <td>方块 Cage</td> <td>铜合金, 镀镍 Copper alloy, Ni plated</td> </tr> <tr> <td>塑件 Housing</td> <td>PA66, UL94V-0</td> </tr> <tr> <th colspan="2">电气性能 ELECTRICAL</th> </tr> <tr> <td>参考标准 Stanard</td> <td>UL IEC</td> </tr> <tr> <td>额定电压 Rated voltage</td> <td>300V 320V</td> </tr> <tr> <td>额定电流 Rated current</td> <td>10A 15A</td> </tr> <tr> <td>使用线径 Wire range</td> <td>24-12AWG 2.5mm²</td> </tr> <tr> <td>接触电阻 Contact resistance</td> <td>20mΩ</td> </tr> <tr> <td>绝缘电阻 Insulation resistance</td> <td>500MΩ/DC500V</td> </tr> <tr> <td>耐电压 Withstanding voltage</td> <td>AC1600V/1Min</td> </tr> <tr> <th colspan="2">机械性能 MECHANICAL</th> </tr> <tr> <td>温度范围 Temp. range</td> <td>-40℃ ~ +105℃</td> </tr> <tr> <td>瞬时温度 Max. soldering</td> <td>+250℃ for 5 Sec</td> </tr> <tr> <td>扭矩 Torque</td> <td>4.08kgf.cm/0.4N.m</td> </tr> <tr> <td>剥线长度 Strip length</td> <td>7~8mm</td> </tr> </table>																		材质及电镀 MATERIAL		螺丝 Screws	M2.5, 钢, 镀锌 M2.5, Steel, Zn plated	夹片 Clamp	铜合金, 镀镍 Copper alloy, Ni plated	方块 Cage	铜合金, 镀镍 Copper alloy, Ni plated	塑件 Housing	PA66, UL94V-0	电气性能 ELECTRICAL		参考标准 Stanard	UL IEC	额定电压 Rated voltage	300V 320V	额定电流 Rated current	10A 15A	使用线径 Wire range	24-12AWG 2.5mm ²	接触电阻 Contact resistance	20mΩ	绝缘电阻 Insulation resistance	500MΩ/DC500V	耐电压 Withstanding voltage	AC1600V/1Min	机械性能 MECHANICAL		温度范围 Temp. range	-40℃ ~ +105℃	瞬时温度 Max. soldering	+250℃ for 5 Sec	扭矩 Torque	4.08kgf.cm/0.4N.m	剥线长度 Strip length	7~8mm												
材质及电镀 MATERIAL																																																																	
螺丝 Screws	M2.5, 钢, 镀锌 M2.5, Steel, Zn plated																																																																
夹片 Clamp	铜合金, 镀镍 Copper alloy, Ni plated																																																																
方块 Cage	铜合金, 镀镍 Copper alloy, Ni plated																																																																
塑件 Housing	PA66, UL94V-0																																																																
电气性能 ELECTRICAL																																																																	
参考标准 Stanard	UL IEC																																																																
额定电压 Rated voltage	300V 320V																																																																
额定电流 Rated current	10A 15A																																																																
使用线径 Wire range	24-12AWG 2.5mm ²																																																																
接触电阻 Contact resistance	20mΩ																																																																
绝缘电阻 Insulation resistance	500MΩ/DC500V																																																																
耐电压 Withstanding voltage	AC1600V/1Min																																																																
机械性能 MECHANICAL																																																																	
温度范围 Temp. range	-40℃ ~ +105℃																																																																
瞬时温度 Max. soldering	+250℃ for 5 Sec																																																																
扭矩 Torque	4.08kgf.cm/0.4N.m																																																																
剥线长度 Strip length	7~8mm																																																																
<p>编码原则 (Product Number Code):</p> <p>WJ2EDGKM-5.08-XXP-1Y-00A</p> <p>产品型号 (Series No.) 间距 (Pitch) 极数 (No. of Poles) 客户需求 (Customer Request) 塑体颜色 (Housing Color)</p> <table border="1"> <tr> <td>1: 单倍间距 (Single Pitch)</td> <td>2: 双倍间距 (Double Pitch)</td> <td>6: 红色 (Red)</td> <td>7: 透明 (Transparent)</td> </tr> <tr> <td>3: 黑色 (Black)</td> <td>4: 绿色 (Green)</td> <td>8: 黄色 (Yellow)</td> <td>9: 白色 (White)</td> </tr> </table>																		1: 单倍间距 (Single Pitch)	2: 双倍间距 (Double Pitch)	6: 红色 (Red)	7: 透明 (Transparent)	3: 黑色 (Black)	4: 绿色 (Green)	8: 黄色 (Yellow)	9: 白色 (White)																																								
1: 单倍间距 (Single Pitch)	2: 双倍间距 (Double Pitch)	6: 红色 (Red)	7: 透明 (Transparent)																																																														
3: 黑色 (Black)	4: 绿色 (Green)	8: 黄色 (Yellow)	9: 白色 (White)																																																														
<table border="1"> <tr> <td colspan="4">第三视角 (THIRD ANGLE PROJECTION)</td> <td colspan="4">插拔式接线端子 PLUG-IN TERMINAL BLOCK</td> </tr> <tr> <td colspan="2">图纸类型 (TYPE)</td> <td colspan="2">CUSTOMER DRAWING</td> <td colspan="2">型号 (NAME)</td> <td colspan="2">WJ2EDGKM-5.08-XXP-1Y-00A</td> </tr> <tr> <td>单位 (UNITS)</td> <td>mm</td> <td>版本 (VERSION)</td> <td>A</td> <td colspan="4"></td> </tr> <tr> <td>尺寸 (SIZE)</td> <td>A4</td> <td colspan="6"></td> </tr> <tr> <td>比例 (SCALE)</td> <td>1:1</td> <td colspan="6"></td> </tr> <tr> <td>图页 (SHEET)</td> <td>1/1</td> <td colspan="6"></td> </tr> </table>																		第三视角 (THIRD ANGLE PROJECTION)				插拔式接线端子 PLUG-IN TERMINAL BLOCK				图纸类型 (TYPE)		CUSTOMER DRAWING		型号 (NAME)		WJ2EDGKM-5.08-XXP-1Y-00A		单位 (UNITS)	mm	版本 (VERSION)	A					尺寸 (SIZE)	A4							比例 (SCALE)	1:1							图页 (SHEET)	1/1						
第三视角 (THIRD ANGLE PROJECTION)				插拔式接线端子 PLUG-IN TERMINAL BLOCK																																																													
图纸类型 (TYPE)		CUSTOMER DRAWING		型号 (NAME)		WJ2EDGKM-5.08-XXP-1Y-00A																																																											
单位 (UNITS)	mm	版本 (VERSION)	A																																																														
尺寸 (SIZE)	A4																																																																
比例 (SCALE)	1:1																																																																
图页 (SHEET)	1/1																																																																
<p>宁波康奈克斯电气有限公司 NINGBO KANGNEX ELECTRIC., LTD.</p>																																																																	