

Specification Sheet

Part Number: 157-00167

One-piece cable tie and fixing offers a simple and easy to use method of bundling and fixing cables, through the design of the fir tree by ensuring positive and secure fixing into panels with thicknesses from 0.6-6.65mm. The offset on the cable tie creates an alternate solution when an offset fixing option is required and a tape clip cannot be used due to the design which reduces the potential of the bundle flexing or shifting.



The 'disc' on the top of the fir tree covers the hole and minimizes the ingress of water and dirt.

1-Pc Cable Tie/Fir Tree Mount, 25mm Offset, 9.1"L, 5.0 mm Hole, 50lb, PA66HIRHS, Gray, 500/pkg

Article Number 157-00167

Type T50ROSFT5SO25A

Color Gray (GY)

Quantity Per carton

Product Description HellermannTyton's Off-Set Fir Tree Cable Tie and fixing offers a simple and easy to use method of bundling and fixing cables, the design of the fir tree ensures a positive and secure fixing into panels with thicknesses from .2" - .26" or threaded blind holes. The 'disc' on the top of the fir tree covers the hole and minimizes the ingress of water and dirt.

Short Description 1-Pc Cable Tie/Fir Tree Mount, 25mm Offset, 9.1"L, 5.0 mm Hole, 50lb, PA66HIRHS, Gray, 500/pkg

Global Part Name T50ROSFT5SO25A-PA66HIRHS-GY

Minimum Tensile Strength (Imperial) 50.0

Minimum Tensile Strength (Metric) 225

Length L (Imperial) 9.1

Length L (Metric) 230.0

Offset Length (Imperial) 0.98

Offset Length (Metric) 25.0

Fixation Method Fir tree for round holes

Identification Plate Position none

Releasable Closure No

Width W (Imperial) 0.20

Width W (Metric) 5.1

Bundle Diameter Min (Imperial) 0.08

Bundle Diameter Min (Metric) 2.0

Bundle Diameter Max (Imperial) 1.97

Bundle Diameter Max (Metric) 50.0

Height H (Imperial)	0.84
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.20
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	5.1
Mounting Hole Diameter D (Imperial)	0.19 - 0.2
Mounting Hole Diameter D (Metric)	4.8 - 5.2 mm
Mounting Hole Diameter D Min (Imperial)	0.19
Mounting Hole Diameter D Max (Imperial)	0.2
Mounting Hole Diameter D Max (Metric)	5.2
Disc Diameter (Imperial)	0.75
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +230°F (-40°C to +110°C)

Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)