







DIM		TOL			
		2--6P	7--12P	13--18P	19--24P
Dim L	(N-1)×5.0+7.0	±0.15	±0.25	±0.35	±0.40
Dim B	(N-1)×5.0	±0.15	±0.25	±0.35	±0.40

SIGN	DATE	DESCRIPTION	APPROVER
	1/29/07	Dim. L changed	Tony
	1/29/07	Soldering temperature changed from 245° to 250°	Tony
	8/01/08	Operating temperature changed	Marvin
THIS IS CAD DRAWING. DO NOT REVISE MANUALLY!!!			

Material:

- Item (a) Contact pin: Brass(CuZn) Tin plated
- Item (b) Terminal(housing): Thermoplastic (UL94V-0)

- Electrical: cULus
- Voltage rating: 300V
 - Current rating: 20A
 - Withstanding Voltage: 1.6 KV
 - ⚠ ● Operating temperature: -40°C to +115°C
 - ⚠ ● Soldering temperature: 250°C±10°C/5 Sec
 - Safety Approval:  ULus

VL xx 7 1 x 0 xxxx G

No. OF POLES —
04: 2x2 POLES
:
:
48: 2x24 POLE

COLOR

- 0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)

— G: Pb<40000ppm

— 0000: "@" Logo
000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	VL-5.0mm Vertical Series						
PART NO.	VLxx71x0xxxxG			DWG NO.	8VL0202		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
	Marvin 2008.08.01	Marvin 2008.08.01	Marvin 2008.08.01		UNIT: mm		X. ±0.50
					SCALE: NONE		X.X ±0.30
					SHEET: 01/01		X.XX ±0.10
					REV.: E	X° ±1°	