







A		B		C		D		E	
REV.	DESCRIPTION				ECN NO.	NAME	DATE		


PRELIMINARY  
DESIGN IS SUBJECT  
TO CHANGE WITHOUT  
PRIOR NOTICE



- NOTES:
- Working temp: -25°C~85°C.
  - Voltage rating: 125V AC/DC(rms)
  - Contact resistance: 55mΩ max.
  - Insulation resistance: 100MΩ min.
  - Current rating: 1A AV/DC
  - Withstanding Voltage: 500V AC/minute
  - Pin Retention Force: 5N min.
  - Housing material: LCP UL94-V0, Natural
  - Terminal mater: Brass,  
plating Ni 40u" min , plating Tin 100u"min.
  - Solder tab material: Brass,  
plating Ni 40u" min , plating Tin 100u"min.



LOCK CONFIGURATION (※※※)



PIN	No.	Dim A	Dim B	Dim C
2	WF-1B125A2P	1.25	3.20	4.30
3	WF-1B125A3P	2.50	4.45	5.55
4	WF-1B125A4P	3.75	5.70	6.80
5	WF-1B125A5P	5.00	6.95	8.05
6	WF-1B125A6P	6.25	8.20	9.30
7	WF-1B125A7P	7.50	9.45	10.55
8	WF-1B125A8P	8.75	10.70	11.80
9	WF-1B125A9P	10.00	11.95	13.05
10	WF-1B125A10P	11.25	13.20	14.30
11	WF-1B125A11P	12.50	14.45	15.55
12	WF-1B125A12P	13.75	15.70	16.80
13	WF-1B125A13P	15.00	16.95	18.05
14	WF-1B125A14P	16.25	18.20	19.30
15	WF-1B125A15P	17.50	19.45	20.55
16	WF-1B125A16P	18.75	20.70	21.80

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				
DIM. TOL.		TITLE: WAFER 1.25mm H3.2mm 90°DIP				
X		DWG. NO.: WF-1B125ANP		DRAWN: MAX		
X.X	±0.30	PART NO.: WF-1B125ANP		CHECKED: ELLA		
X.XX	±0.25	UNIT: mm		APPROVED: WILL		
X.XXX	±0.15	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	
GENERAL ANGLE: ±3°						