



SIGN	DATE	DESCRIPTION	APPROVER
⚠1	08/24'12	Change the dwg no 8H60102 to 8H60801	Da cheng
		THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!	



PCB Layout







Material:

- Item ① Lever: Thermoplastic (UL94V-0)
- Item ② Terminal body: Thermoplastic (UL94V-0)
- Item ③ Terminal side body: Thermoplastic (UL94V-0)
- Item ④ Pad board: Thermoplastic (UL94V-0)
- Item ⑤ cover: Thermoplastic (UL94V-0)
- Item ⑥ Spring clamp: Stainless steel
- Item ⑦ contact pin: Brass.Tin plated

Electrical:	cULus	VDE
Voltage rating:	300 V	450 V
Current rating:	11 A	12 A
Wire range:	0.5-4mm²	
Solid wire(AWG):	12-20	
Stranded wire(AWG):	12-20	
Wire strip length:	10-11 mm	
Withstanding Voltage:	1.6KV	
Operating temperature:	-40°C to +115°C	
Soldering temperature:	260°C ±5°C/5 Sec	
Safety Approval:		
Critical dimension:		

H6 xx 2 0 x 0 xxxx G

No. OF POLES
02: 2 POLES
:
:
12: 12 POLES

COLOR
0: BLACK
5: GREEN (RAL 6018/T)
6: BLUE
8: GREY (RAL 7004/P)

RoHS compliant
(lead<4%)
In copper Alloy

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark

Any special item by customer requst. please contact sales department.

N=NUMBER OF POLES

DIM		TOL			
		2P--4P	5P--7P	8P--10P	11P--12P
Dim A	(N-1)×10.0+6.50	±0.15	±0.20	±0.30	±0.40
Dim B	(N-1)×10.0	±0.15	±0.20	±0.25	±0.30

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	H6 10.0mm Series (Round hole)				
PART NO.	H6xx20x0xxxxG			DWG NO.	8H60801 ⚠1
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Da cheng 2012.08.24	Da cheng 2012.08.24	UNIT: mm SCALE: NONE SHEET: 01/01 REV.: B	Tolerance X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°