

SIGN	DATE	DESCRIPTION	APPROVER
1	07/02`11	No. OF POLES is changed	Runner
2	09/24`11	Add is "cULus" mark	Runner
		THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!	





PCB Layout

N = Number of poles.
Dim.A = N×5.0+1.0
Dim.B = (N-1)×5.0

POLE	4×2 ~ 4×6	4×7 ~ 4×12	4×13 ~ 4×18	4×19 ~ 4×24
Dim.A	±0.15	±0.25	±0.35	±0.45
Dim.B	±0.15	±0.25	±0.30	±0.40

Material:

- Item Ⓐ Insulator(Cover): Thermoplastic (UL94V-0)
- Item Ⓑ Insulator(housing): Thermoplastic (UL94V-0)
- Item Ⓒ Spring clamp: Stainless steel
- Item Ⓓ Solder Pin (The fourth layer) : Brass, Tin plated
- Item Ⓔ Solder Pin (The third layer) : Brass, Tin plated
- Item Ⓕ Solder Pin (The second layer) : Brass, Tin plated
- Item Ⓖ Solder Pin (The first layer) : Brass, Tin plated

Electrical:	cULus
Voltage rating:	300V
Current rating:	10A
Wire range:	
Solid wire(AWG):	12-28
Stranded wire(AWG):	12-28
Wire strip length:	6-7mm
Withstanding Voltage:	1.6KV
Operating temperature:	-40°C to +115°C
Soldering temperature:	250°C±10°C/5 Sec
Safety Approval:	c UL us
Critical dimension:	▽

HS xx 0 0 x 1 xxxx G

No. OF POLES
08: 4×2 POLES
:
92: 4×23 POLES
96: 4×24 POLES

COLOR
0: BLACK
5: GREEN (RAL 6018/T)
6: BLUE
8: GREY (RAL 7004/P)

G: Pb<40000ppm

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by customer requst. please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	HS 5.0mm Series (Solder pins staggered by half the pin spacing)				
PART NO.	HSxx00x1xxxxG			DWG NO.	8HS0102
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Runner 2011.09.24	Kind 2009.6.8	UNIT: mm SCALE: NONE SHEET: 01/01 REV.: D	

Tolerance	
X.	±0.50
X.X	±0.30
X.XX	±0.10
X°	±1°