




Cable Assemblies > Copper Cable Assemblies > Internal I/O Cable Assemblies



Cable Assembly Type: **CT**

Number of Positions: **3**

Cable Assembly Length: **.3 m**

Cable Style: **Discrete Pair**

Wire Size: **28 AWG**

## Features

### Product Type Features

Cable Assembly Type	CT
Cable Style	Discrete Pair

### Configuration Features

Number of Positions	3
Number of Signal Positions	3

### Other

Cable Assembly Length	.3 m
EU RoHS Compliance	Compliant

### Dimensions

Wire Size	28 AWG
-----------	--------

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 292207-3  
MINI CT SGL DIP V 3P NAT



TE Part # 292230-3  
1.5 MINI CT SGL V SMT W/BOSS 3



TE Part # 292227-3  
1.5 MINI CT SGL H SMT W BOSS 3



TE Part # 292215-3  
MINI CT SGL RELAY 3P NAT



TE Part # 292228-3  
1.5 MINI CT SGL H SMT W/O BOSS




TE Part # 2106091-2  
3 pos Inverted Thru Board SMT Header



TE Part # 292206-3  
MINI CT SGL DIP H 3P NAT


## Customers Also Bought



TE Part #3-520339-2  
ULTRA-FAST 187 ASY REC 16-14 AWG  
TPBR



TE Part #1622796-6  
YR1 0.1% 10K




TE Part #2405870-4  
CT 4P 300MM CABLE ASSEMBLY 6-  
353908-4




TE Part #1-338068-0  
MICRO-MATCH FTE,10P




TE Part #T41613B9L25-002  
RPC-M12L-5FS-1.0-SH PUR 14AWG GY




TE Part #8-2176554-5  
3430 A2 1% 3K0 100ppm 1k RL




TE Part #8-2176554-6  
3430 A2 1% 3K3 100ppm 1k RL



TE Part #9-2176554-0  
3430 A2 1% 4K7 100ppm 1k RL



TE Part #8-2176558-4  
3430 B2 1% 2K7 100ppm 1k RL



TE Part #3198143001  
ACW0219-2.50-9(NS)

## Documents

### Product Drawings

[CT 3P 300MM CABLE ASSEMBLY 6-353908-3](#)

English

### CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_2405870-3\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2405870-3\\_A.3d\\_igs.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_2405870-3\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

2405870-3

CT Cable Assembly, 3 Position, .3 m, 28 AWG, 3 Signal Positions



[6-1773454-5\\_AMP\\_Mini\\_CT\\_Connector\\_Series\\_QRG](#)

English