



Part Number : [1300350068](#)

Product Description : DeviceNet Trunk Mini-Change Segmented Power Tee, 5 Pole, Male/Female with Female Drop

Series Number : 130035

Status : Active

Product Category : Industrial Tees and Splitters

Engineering Number : DN3030-PT-1



Documents & Resources

Drawings

[1300350068_sd.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|--|
| GADSL/IMDS | Not Relevant |
| China RoHS | Not Reviewed per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21 |
| REACH SVHC | Not Reviewed per D(2024)4144-DC (27 June 2024) |
| EU RoHS | Not Reviewed per EU 2015/863 |

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

| | |
|----------------|---|
| Status | Active |
| Category | Industrial Tees and Splitters |
| Series | 130035 |
| Description | DeviceNet Trunk Mini-Change Segmented Power Tee, 5 Pole, Male/Female with Female Drop |
| IP Rating | IP67 |
| Product Family | DeviceNet Solutions |
| Product Name | DeviceNet Trunk |
| Type | Drop Tee |
| UPC | 78678887060 |

Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 8.0A |
| Voltage - Maximum | 600V |

Physical

| | |
|---------------------------|-------------------------|
| Color - Cable Jacket | Gray |
| Drop Connector | Mini-Change |
| Drop Gender | Female |
| Keyway | Single |
| LED Indicator | No |
| Left Trunk Connector | Mini-Change |
| Left Trunk Gender | Male |
| Leg 1 Length | N/A |
| Leg 2 Length | N/A |
| Material - Cable Jacket | N/A |
| Material - Connector Body | TPE |
| Material - Coupling Nut | Black Epoxy Coated Zinc |
| Net Weight | 93.439/g |

| | |
|-------------------------------|----------------|
| Poles | 5 |
| Right Trunk Connector | Mini-Change |
| Right Trunk Gender | Female |
| Temperature Range - Operating | -20° to +105°C |

This document was generated on Oct 14, 2024