


1

2

3


4

A





A

B



B

C



C

Technical requirements:

- 1、 Unit: mm
- 2、 Wire diameter: 0.4
- 3、 Material: Nickel Plated Steel-Wire, meet ROHS
- 4、 Style: horn mouth without pin
- 5、 Technics: High-Temperature Heat Treatment at 260°C
- 6、 Size tolerance: The tolerance of unmarked parts is $\pm 0.25\text{mm}$
- 7、 No dirty surface, no bad material
- 8、 Contact number: 13459252012、 0592-5216722
- 9、 Mode: F8.7-8.5-6-0.4N
- 10、 Salt spray test: five percent salt spray test meets 24hours
- 11、 Package: by bag, MPQ: 2000PCS/bag

D

D

E

E

						碳钢线			厦门市芯网电子科技有限公司	
标记	处数	分区	更改文件号	签名	年月日	阶段标记	重量	比例		
设计						s		3:1		
校核										
批准										

F

F

1

2

3

4