KUP-14AT5-120 ✔ ACTIVE

Potter & Brumfield | Potter & Brumfield KUP

TE Internal #: 7-1393117-1

General Purpose Power Relay, Monostable, 2.9 VA Coil Power Rating AC, 1700 ohm Coil Resistance, Potter & Brumfield KUP, Power Relays

View on TE.com >

Relays & Contactors > Relays > Power Relays



Relay Type: **General Purpose Power Relay**

Coil Magnetic System: **Monostable**

Coil Power Rating Class: **[2 – 3 VA]**

Coil Power Rating AC: **2.9 VA**

Coil Resistance: **1700 Ω**

Features

Product Type Features

Relay Type	General Purpose Power Relay

Configuration Features

Coil Special Features	UL Coil Insulation Class B
Contact Arrangement	3 Form C 3PDT-CO
Contact Number of Poles	3

Electrical Characteristics

Contact Limiting Short-Time Current	10 A
Contact Limiting Continuous Current	10 A
Insulation Initial Dielectric Between Open Contacts	1200 Vrms
Contact Limiting Making Current	10 A
Insulation Initial Dielectric Between Adjacent Contacts	2200 Vrms
Insulation Initial Dielectric Between Contacts & Coil	2200 Vrms
Insulation Initial Resistance	100 MΩ
Contact Limiting Breaking Current	10 A
Coil Power Rating AC	2.9 VA
Coil Resistance	1700 Ω
Coil Voltage Rating	120 VAC
Contact Current Rating	10 A

Contact Switching Load (Min)	300mA @ 12V
Contact Voltage Rating	240 VAC

Body Features

Product Weight	85 g[2.988 oz]

Contact Features

Contact Material	AgCdO

Termination Features

Relay Connection Type	Plug-In
Terminal Configuration	Quick Connect Terminals

Mechanical Attachment

Product Mounting Feature Type	Flange with Mounting Slots
Product Mount Type	Panel

Dimensions

Product Width	38.56 mm[1.51 in]
Product Length	50.52 mm[1.98 in]
Product Height	57.1 mm[2.24 in]

Usage Conditions

Environmental Category of Protection	RTI
Environmental Ambient Temperature (Max)	45 °C[113 °F]
Operating Temperature Range	-45 – 45 °C

Operation/Application

Current Type	AC
Coil Magnetic System	Monostable

Packaging Features

Packaging Method	Package

Other

Length Class (Mechanical)	35 – 40 mm
Environmental Ambient Temperature Class	0 – 50 °C
Width Class (Mechanical)	30 – 40 mm
	2 – 3 VA
Contact Current Class	16 A

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: Cadmium oxide (4.37% in Component Part) **Article Safe Usage Statements:** Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 9-1393117-9
KUP-14A55-120=KU




TE Part # 6-1393117-7
KUP-14AE5-120=KU



TE Part # 6-1393117-9
KUP-14AE5-240=KU

Also in the Series | Potter & Brumfield KUP



Power Relays(71)




Relay Accessories(10)

Customers Also Bought




TE Part #1027-003-1200
CLIP, SS, 11MM HOLE, ST



TE Part #350390-1
.140 DIA SOK 14-10 PTPBR L/P




TE Part #3-520150-2
ULTRA-FAST 187 ASY REC 16-14 AWG TPBR



TE Part #350391-1
.140 DIA PIN 14-10 PTPBR L/P



TE Part #8-1393117-0
KUP-14A15-240=KU



TE Part #1SNK150000R0000
MC612



TE Part #1SNK516010R0000
ZS35



TE Part #8-1618404-5
EV200DAANA=CONTACTOR, SPST-NC



TE Part #1423159-3
7012NC=RLY,STD,ON,2P,48VDC,15



TE Part #2-1437463-1
SCERX22ABA=120V &125VDC 0.5 TO

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_7-1393117-1_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_7-1393117-1_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_7-1393117-1_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

KU Sockets & Accessories

English

KUP Series Panel Plug-in Relay

English

Product Specifications

Definitions General Purpose Relays

English

Agency Approvals

UL

English