

1SNG612001R0000 ✓ ACTIVE

ENTRELEC

TE Internal #: 1SNG612001R0000

Drain Plug, Brass, Nickel

[View on TE.com >](#)



Wire Protection & Management > Cable Glands > EM-DRP-1SNG612



Cable Gland Product Type: **Drain Plug**

Primary Product Material: **Brass**

Primary Product Plating Material: **Nickel**

Sealable: **Yes**

Operating Temperature Range: **-60 – 85 °C [-76 – 185 °F]**

[All EM-DRP-1SNG612 \(8\)](#)

Features

Product Type Features

Cable Gland Product Type	Drain Plug
Sealable	Yes

Body Features

Primary Product Material	Brass
Primary Product Plating Material	Nickel

Usage Conditions

Operating Temperature Range	-60 – 85 °C [-76 – 185 °F]
-----------------------------	------------------------------

Packaging Features

Packaging Method	Bag
------------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
------------------------------	---------------

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2023
(235)Candidate List Declared Against: JAN 2023
(233)

SVHC > Threshold:

Pb (3% in Component Part)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Documents

Product Drawings[EM-DRP-M20-MET-A](#)

English

CAD Files[3D PDF](#)

3D

Customer View Model[ENG_CVM_CVM_1SNG612001R0000_A.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_1SNG612001R0000_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1SNG612001R0000_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Catalog - ENTRELEC Cable Glands](#)

English

Agency Approvals

[UL](#)

English

[UL](#)

English