





RoHS



NOTE:

- 1.Rating: 24V 25mA DC
- 2.Insulation Resistance: $\geq 100 \text{ M}\Omega$
- 3.Withstand voltage: AC 500V 1Minute
- 4.Operating Force Range: 1000gf Max
- 5.Mechanical Life: 3,000 Cycles

Ⓕ	Dust film		1	Polyimide tape	
Ⓖ	Terminal		10	Phosphor bronze	Gold plating
Ⓓ	Contact spring		5	Phosphor bronze	Gold plating
Ⓒ	Handle		5	PA46	White
Ⓑ	Cover		1	PPS	Black
Ⓐ	Base		1	PPS	Black
NO.	Name	Number	Qty	Materil	Remarks

YUANDI® Yuandi Electronics Co.,Ltd

design	date	name	DIP SWITCH
Review	date	model	TP-05
Approved	date		

Drawing number: Proportion 1:1 unit mm gage number A4

modify Review Approved

angle	$\pm 2^\circ$
10~30	± 0.30
5~10	± 0.20
~ 5	± 0.10

Tolerance not specified