

MAT'L NO. (LOOSE PIECE)	ENG. NO.	MAT'L NO. (TAPE MOUNTED)	ENG. NO.	STUD SIZE	"S" ±.005 (0.13)	STOCK THICKNESS	FINISH
190690200	C-128-04	190690147	C-128-04T	4	.126 (3.20)	COPPER .040 (1.02)	SEE NOTE 1
190690202	C-128-06	- - - - -	- - - - -	6	.146 (3.71)		
190690205	C-128-08	190690208	C-128-08T	8	.173 (4.39)		
190690209	C-128-10	190690212	C-128-10T	10	.198 (5.03)		
190690215	C-128-209	- - - - -	- - - - -	209	.209 (5.18)		
192030159	C-U-128-06	- - - - -	- - - - -	6	.146 (3.71)	NICKEL .038 (0.97)	NONE
192030160	C-U-128-08	- - - - -	- - - - -	8	.173 (4.39)		
192030113	C-U-128-10	192030114	C-U-128-10T	10	.198 (5.03)		
190690682	C-128-10-AU	- - - - -	- - - - -	10	.198 (5.03)	COPPER .040 (1.02)	SEE NOTE 2





NOTES:

1. FINISH: TIN PLATING, 100 µin (2.5 µm) MIN
2. FINISH: GOLD, 50 µin (1.25 µm) MIN. OVER NICKEL, 50 µin (1.25 µm) MIN. PLATING.
3. WIRE SIZE: 12-10 AWG
4. PARTS ARE RoHS COMPLIANT.

A4

DOCUMENT STATUS	P1	RELEASE DATE	2023/07/18 21:49:57				

FORMAT: Eng-legal-portrait-prod-B
REVISION: D
DATE: 2018/01/18

SYMBOLS: E = 0; E = 0; E = 0; E = 0; ▼ = 0; E = 0; ☒ = 0; ■ = 0; ▽ = 0

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS: INCH/MM
SCALE: 1:1

GENERAL TOLERANCES (UNLESS SPECIFIED)

	MM	INCH
4 PLACES	±	±
3 PLACES	±	±
2 PLACES	±	±
1 PLACE	±	±
0 PLACES	±	±
ANGULAR TOL	± °	

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC: CORRECTED TYPO IN NOTES, REMOVED METRIC CONVERSION: WAS 4.0-6.0

EC NO: 757040
DRWN: DEANNM1 2023/07/14
CHK'D: ETHRODAHL 2023/07/18
APPR: ETHRODAHL 2023/07/18

INITIAL REVISION:
DRWN:
APPR:

THIRD ANGLE PROJECTION | DRAWING: B-SIZE | SERIES: 19069

molex

RING TONGUE TERMINAL
KRIMPTITE, 128 SERIES 12-10 AWG

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
SD-19069-020	PSD	001	A4

MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
	GENERAL MARKET	1 OF 1