STRADA-2X2-C-STP

Beam for area and street lighting such as parks and pedestrian walkways



SPECIFICATION:

Dimensions	50.0 x 50.0 mm
Height	5.3 mm
Fastening	pin, screw
ROHS compliant	yes


MATERIALS:

Component	Type	Material	Colour	Finish
STRADA-2X2-C-STP	Multi-lens	PMMA	clear	

ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
C13937_STRADA-2X2-C-STP » Box size: 476 x 273 x 292 mm	800	160	160	5.5

LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.



See also our general installation guide: www.ledil.com/installation_guide


LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

OPTICAL RESULTS (MEASURED):

bridgelux


LED	Bridgelux SMD 5050
FWHM / FWTM	131.0° / 156.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	






COMET ELECTRONICS

LED	QUICK FLUX XTP 2x4 xxx LS G5
FWHM / FWTM	138.0° / 161.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	




COMET ELECTRONICS

LED	QUICK FLUX XTP 2x6 xxx LS G5
FWHM / FWTM	138.0° / 160.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



CREE LEDs

LED	J Series 5050C 6V E Class
FWHM / FWTM	Asymmetric
Efficiency	97 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.


OPTICAL RESULTS (MEASURED):

CREE LEDs

LED	XM-L3
FWHM / FWTM	Asymmetric
Efficiency	97 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:






CREE LEDs

LED	XP-G2
FWHM / FWTM	137.0° / 158.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:




CREE LEDs

LED	XP-G3
FWHM / FWTM	141.0° / 164.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:






CREE LEDs

LED	XP-L HD
FWHM / FWTM	139.0° / 166.0°
Efficiency	92 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:




LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

OPTICAL RESULTS (MEASURED):

CREE LEDs


LED	XP-L HI
FWHM / FWTM	136.0° / 162.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



CREE LEDs

LED	XP-L2
FWHM / FWTM	139.0° / 166.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	






LUMILEDS


LED	LUXEON 5050 Round LES
FWHM / FWTM	121.0° / 146.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	





LUMILEDS

LED	LUXEON MZ
FWHM / FWTM	133.0° / 156.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	




LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

OPTICAL RESULTS (MEASURED):

LUMILEDS


LED	LUXEON TX
FWHM / FWTM	133.0° / 156.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



LUMILEDS


LED	LUXEON V
FWHM / FWTM	136.0° / 166.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	






LUMINUS

LED	SST-10-B130
FWHM / FWTM	127.0° / 154.0°
Efficiency	97 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	Deep Red
Required components:	



MST Your solutions

LED	RecLED 122x50mm 1900lm 730 2x4 Opt G1
FWHM / FWTM	Asymmetric
Efficiency	98 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	




LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

OPTICAL RESULTS (MEASURED):


NICHIA

LED	NVSW219F
FWHM / FWTM	131.0° / 155.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



NICHIA


LED	NVSW319B
FWHM / FWTM	139.0° / 162.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



NICHIA


LED	NVSW3x9A
FWHM / FWTM	138.0° / 165.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	





OSRAM

LED	PrevaLED Brick HP 2x8
FWHM / FWTM	137.0° / 157.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	




LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

OPTICAL RESULTS (MEASURED):

OSRAM
Opto Semiconductors

LED	Duris S8
FWHM / FWTM	131.0° / 154.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White


Required components:



OSRAM
Opto Semiconductors

LED	OSLON Square CSSRM2/CSSRM3
FWHM / FWTM	137.0° / 157.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White


Required components:



OSRAM
Opto Semiconductors

LED	OSLON Square PC
FWHM / FWTM	130.0° / 161.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White


Required components:



PHILIPS

LED	Fortimo FastFlex LED 2x8 DA G4
FWHM / FWTM	136.0° / 161.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:




LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

OPTICAL RESULTS (MEASURED):


PHILIPS

LED	Fortimo FastFlex LED 2x8 DA G4+
FWHM / FWTM	130.0° / 157.0°
Efficiency	97 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



PHILIPS


LED	Fortimo FastFlex LED 2x8 DA G5
FWHM / FWTM	124.0° / 151.0°
Efficiency	98 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



PHILIPS


LED	Fortimo FastFlex LED 2x8 DAX G4
FWHM / FWTM	141.0° / 164.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	





SAMSUNG

LED	HiLOM RC12 Z (LH181B)
FWHM / FWTM	118.0° / 145.0°
Efficiency	99 %
Peak intensity	0.4 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	




LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

OPTICAL RESULTS (MEASURED):

SAMSUNG

LED	HiLOM RH12 Z (LH351C)
FWHM / FWTM	133.0° / 160.0°
Efficiency	97 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White


Required components:



SAMSUNG

LED	HiLOM RH16 (LH351C)
FWHM / FWTM	Asymmetric
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White


Required components:



SAMSUNG

LED	HiLOM RM12 Z (LH502C)
FWHM / FWTM	121.0° / 150.0°
Efficiency	97 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White


Required components:



SAMSUNG

LED	HiLOM RM16 Z (LH502C)
FWHM / FWTM	122.0° / 152.0°
Efficiency	99 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:




LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

OPTICAL RESULTS (MEASURED):

SAMSUNG

LED	HiLOM RM8 Z (LH502C)
FWHM / FWTM	123.0° / 153.0°
Efficiency	98 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White


Required components:



SAMSUNG

LED	LH351B
FWHM / FWTM	134.0° / 158.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White


Required components:



SAMSUNG

LED	LH351Z
FWHM / FWTM	127.0° / 153.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White


Required components:



SAMSUNG

LED	LH508A
FWHM / FWTM	Asymmetric
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:



LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

OPTICAL RESULTS (MEASURED):

SEITEC Elektronik GmbH


LED	LED-Pa-L15c2W11c2-xxx-C050-01
FWHM / FWTM	124.0° / 148.0°
Efficiency	98 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:

SEOUL SEMICONDUCTOR

LED	Z5M3
FWHM / FWTM	Asymmetric
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White


Required components:



SEOUL SEMICONDUCTOR

LED	Z5M4
FWHM / FWTM	120.0° / 142.0°
Efficiency	98 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White


Required components:



SEOUL SEMICONDUCTOR

LED	Z8Y22
FWHM / FWTM	117.0° / 146.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:



LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.


OPTICAL RESULTS (MEASURED):

SEOUL SEMICONDUCTOR

LED	Z8Y22P
FWHM / FWTM	136.0° / 163.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:






TOSHIBA
Leading Innovation

LED	TL1L4
FWHM / FWTM	119.0° / 143.0°
Efficiency	92 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:



TRIDONIC


LED	RLE 2x4 2000lm HP EXC2 OTD
FWHM / FWTM	137.0° / 159.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:

TRIDONIC

LED	RLE 2x8 4000lm HP EXC2 OTD
FWHM / FWTM	137.0° / 159.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:




LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

OPTICAL RESULTS (MEASURED):


TRIDONIC

LED	RLE G1 49x121mm 2000lm xxx EXC OTD
FWHM / FWTM	129.0° / 158.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	




TRIDONIC

LED	RLE G1 49x133mm 2000lm xxx EXC OTD
FWHM / FWTM	129.0° / 158.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	




TRIDONIC

LED	RLE G1 49x223mm 4000lm xxx EXC OTD
FWHM / FWTM	129.0° / 158.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



TRIDONIC

LED	RLE G1 49x245mm 4000lm xxx EXC OTD
FWHM / FWTM	129.0° / 158.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	




LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

OPTICAL RESULTS (SIMULATED):

CREE LEDs


LED	XP-G2 HE
FWHM / FWTM	130.0° / 146.0°
Efficiency	95 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



CREE LEDs


LED	XP-G3
FWHM / FWTM	128.0° / 148.0°
Efficiency	84 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	

Protective plate, glass




LUMILEDS

LED	LUXEON 3030 2D (Round LES)
FWHM / FWTM	119.0° / 141.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



LUMILEDS

LED	LUXEON 3030 2D (Square LES)
FWHM / FWTM	121.0° / 143.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.


OPTICAL RESULTS (SIMULATED):

LUMILEDS

LED	LUXEON 5050 HE
FWHM / FWTM	120.0° / 143.0°
Efficiency	87 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:


Protective plate, glass



LUMILEDS

LED	LUXEON 5050 HE
FWHM / FWTM	122.0° / 145.0°
Efficiency	96 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:




LUMILEDS

LED	LUXEON 5050 Round LES
FWHM / FWTM	120.0° / 141.0°
Efficiency	88 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:


Protective plate, glass



LUMILEDS

LED	LUXEON 5050 Square LES
FWHM / FWTM	120.0° / 143.0°
Efficiency	96 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:



LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.


OPTICAL RESULTS (SIMULATED):

LUMILEDS

LED	LUXEON 5050 Square LES
FWHM / FWTM	120.0° / 141.0°
Efficiency	88 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:


Protective plate, glass



LUMILEDS

LED	LUXEON HL2Z
FWHM / FWTM	118.0° / 136.0°
Efficiency	95 %
Peak intensity	0.4 cd/lm
LEDs/each optic	1
Light colour	White

Required components:




LUMILEDS

LED	LUXEON HL2Z
FWHM / FWTM	117.0° / 134.0°
Efficiency	87 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:


Protective plate, glass



LUMILEDS

LED	LUXEON XR-HL2X (L2H2-xxxxxxxMLU010)
FWHM / FWTM	126.0° / 138.0°
Efficiency	96 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:



LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.


OPTICAL RESULTS (SIMULATED):

LUMILEDS

LED	LUXEON XR-HL2X (L2H2-xxxxxxxMLU010)
FWHM / FWTM	124.0° / 138.0°
Efficiency	86 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:

Protective plate, glass




NICHIA

LED	NF2x757G
FWHM / FWTM	120.0° / 141.0°
Efficiency	87 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:


Protective plate, glass



NICHIA

LED	NV4WB35AM
FWHM / FWTM	124.0° / 147.0°
Efficiency	96 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White


Required components:



NICHIA

LED	NVSW219D
FWHM / FWTM	120.0° / 140.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:




LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

OPTICAL RESULTS (SIMULATED):


NICHIA

LED	NVSxE21A
FWHM / FWTM	118.0° / 138.0°
Efficiency	94 %
Peak intensity	0.4 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



OSRAM
Opto Semiconductors


LED	OSCONIQ P 3737 (3W version)
FWHM / FWTM	116.0° / 144.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



OSRAM
Opto Semiconductors


LED	OSLON Square CSSRM2/CSSRM3
FWHM / FWTM	124.0° / 144.0°
Efficiency	84 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	

Protective plate, glass



PHILIPS

LED	Fortimo FastFlex LED 2x8 DA HE
FWHM / FWTM	122.0° / 140.0 + 138.0°
Efficiency	97 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.


OPTICAL RESULTS (SIMULATED):

PHILIPS

LED	Fortimo FastFlex LED 2x8 DA HE
FWHM / FWTM	120.0° / 140.0 + 138.0°
Efficiency	86 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:

Protective plate, glass




SAMSUNG

LED	HiLOM RH12 Z (LH351C)
FWHM / FWTM	123.0° / 144.0°
Efficiency	86 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:


Protective plate, glass



SAMSUNG

LED	LH351D
FWHM / FWTM	123.0° / 140.0°
Efficiency	91 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White


Required components:



SEOUL SEMICONDUCTOR

LED	MJT 5050
FWHM / FWTM	121.0° / 143.0°
Efficiency	96 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:




LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

OPTICAL RESULTS (SIMULATED):

SEOUL SEMICONDUCTOR

LED	SEOUL DC 5050 6V
FWHM / FWTM	112.0° / 140.0°
Efficiency	94 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy
Joensuunkatu 13
FI-24240 SALO
Finland

LEDiL Inc.
228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.
405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support
www.ledil.com/
where_to_buy

Shipping locations
Salo, Finland
Hong Kong, China

Distribution Partners
www.ledil.com/
where_to_buy

LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.