

FRED

Ultrafast Soft Recovery Diode, 650V, 30A

Description:

These diodes are optimized to less losses and EMI/RFI in high frequency power conditioning system. The soft recovery character of the diodes offers buffer in most applications. These devices are suited for power converters and other applications where the switching losses are not significant portion of the total losses.


Features:

- Ultrafast Recovery
- 175°C operating junction temperature
- High frequency operation
- Low IR value
- High surge capacity
- Epitaxial chip construction

Product Summary	
V_R	650 V
$I_{F(AV)}$	30 A
t_{rr}	40 ns

Applications:

- Switched mode power supply
- Free wheeling diode
- UPS



Absolute Maximum Ratings						
Parameter	Symbol	Test Conditions	Values			Units
Repetitive peak reverse voltage	V_{RRM}		650			V
Continuous forward current	$I_{F(AV)}$	$T_A=110^\circ\text{C}$	30			A
Single pulse forward current	I_{FSM}	$T_A=25^\circ\text{C}$	300			A
Maximum repetitive forward current	I_{FRM}	Square wave, 20kHz	75			A
Operating junction	T_j		175			°C
Storage temperatures	T_{stg}		-55 to +175			°C
Electrical characteristics ($T_A=25^\circ\text{C}$ unless otherwise specified)						
Parameter	Symbol	Test Conditions	Min.	Typ.	Max.	Units
Breakdown voltage Blocking voltage	V_{BR}	$I_R=100\mu\text{A}$	650			V
	V_R					
Forward voltage	V_F	$I_F=75\text{ A}$		1.35	1.65	V
		$I_F=75\text{ A}, T_j=125^\circ\text{C}$		1.25	1.50	V
Reverse leakage current	I_R	$V_R=V_{RRM}$			30	μA
		$T_j=150^\circ\text{C}, V_R=650\text{V}$			300	μA
Reverse recovery time	t_{rr}	$I_F=0.5\text{A}, I_R=1\text{A}, I_{RR}=0.25\text{A}$			55	ns
		$I_F=1\text{A}, V_R=30\text{V}, di/dt=200\text{A}/\mu\text{s}$		28	40	ns
Thermal characteristics						
Parameter	Symbol	Typ	MAX			Units
Junction-to-Case	R_{thJC}	-	2.8			°C/W




Figure 1. Forward Characteristic(typ.)




Figure 2. Reverse Characteristic (typ.)

Package Information		
TO-220C-2 PACKAGE		
Symbol	Dimensions(millimeters)	
	Min.	Max.
A	4.30	4.70
A1	1.20	1.40
A2	2.30	2.50
b	0.60	1.00
b1	1.15	1.55
c	0.40	0.60
e	4.88	5.28
E	9.80	10.20
H	15.50	15.90
H1	9.00	9.40
H2	12.50	13.50
H3	2.80	3.20
G	2.60	3.00
ΦP	3.40	3.80