



1. FIGURE AND DIMENSIONS (视图及尺寸)



端面
X0600HI-XX-LPHF

XXXXXT-XXXX-XXX-AXXXX-LXXX-XXXXXT-X
① ② ③ ④ ⑤ ⑥ ⑦

- ① 系列 (Series No)
- ② Pin位 (Pin bit)
- ③ 材质 (Material) :P-PSN(磷铜先冲后镀锡)
- ④ 线规线色 (Wire gauge line color) A: (AWG20-AWG24)
Circuit: R(red)/B (black) /Y (yellow) /G (green) /
L (blue) /P (purple) /YR (orange) /W (white) /E(grey)/N (brown)
- ⑤ 线长 (Line length) L: (可定制长度)
- ⑥ 系列 (Series No)
- ⑦ 正反接或镀锡 (Front and reverse or tin-plated) Z(反接)/F (正接) TX (镀锡Xmm)

2. CIRCUIT DIAGRAM (接线图)

A	颜色	B
Circuit1	红色	
Circuit2	黑色	

3. MATERIAL (材料)

标志	料号	单用量	备注	总用量
1	X0600HI-02-LP HF	1PCS		
2	UL10064/34AWG. 红. 黑色	红黑各 1PCS/	100MM	
总量				

					ANGLAR	±5°	XKLB	DSND		SCALE: N/A	DRAWING NO. X0600T-02-PV01-A34RB-L100-T3		
					L ≤ 4	±0.2		DWN		VIEW:	PART NO.:		
					4 < L ≤ 16	±0.3		CHKD		UNIT: mm/in	DWG NO.:		
					16 < L ≤ 63	±0.4		APPD		SIZE: A4			
					L > 63	±0.5							
					UNSPECIFIED TOLERANCES			XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT	SHEET	REVISION
												1/1	A0