





- 1.PUSH BUTTON SWITCH MODEL NO. MPS11-ML180-R (0.5mm)  
2.SOLDERING TYPE, LONG TERMINAL  
3.RATING:16A 125VAC 10A 250VAC(C-UL)  
TV-5(C-UL)  
5A/80A 250V~ $\mu$ T85/55(NEMKO;CB)  
5A/80A 250V~ $\mu$ T85(ENEC17)  
16A 250VAC 5/80A 250V~ $\mu$ T125(CQC)  
4.SILVER CONTACT:Ag ALLOY(t=0.5mm) CLAD COPPER ALLOY  
5.ALL MATERIALS USE IN CONFORMIY WITH THE RoHS DIRECTIVE

电话：0769-82310511867

邮箱：hooya89@hooya.hk

V：hooya89



|    |             |    |             |                        |           |                                        |         |        |            |                         |     |             |      |
|----|-------------|----|-------------|------------------------|-----------|----------------------------------------|---------|--------|------------|-------------------------|-----|-------------|------|
| 5  |             | 10 |             | DIMENSIONAL TOLERANCES |           | APPROVED                               | CHECKED | DESIGN | DRAWN      | ALL SIZE ARE IN         | MM  |             |      |
| 4  |             | 9  |             | RANGE                  | TOLERANCE |                                        |         |        | LMC        | SCALE                   | NO  |             |      |
| 3  |             | 8  |             | X                      | ±0.30     |                                        |         |        | 2019.05.20 | MAT'L                   | *** |             |      |
| 2  |             | 7  |             | X.X                    | ±0.20     |                                        |         |        |            | MATERIAL NO.            |     | DRAWING NO. | REV. |
| 1  |             | 6  |             | X.XX                   | ±0.10     |                                        |         |        |            | MPS11-ML180-B(0.5mm)16A |     | WIF119051   | A    |
| NO | DESCRIPTION | NO | DESCRIPTION | ANGLES                 | ±1°       | LEGION ELECTRONIC & HARDWARE CO., LTD. |         |        |            |                         |     |             |      |