





# RoHS



技术要求:

- 1.打铜底0.5-1 $\mu$ m,镍2-2.5 $\mu$ m, 镀雾锡3-5 $\mu$ m。
- 2.铆好后不得有松动现象。
- 3.插脚尖部符合可焊性要求。
- 4.螺纹需符合通止规/止针要求。
- 5.螺纹扭矩: 2.0Nm.
- 6.额定电流: 100A.



>30.±0.4	X.°±
6-30±0.3	.X°±
0-6±0.2	.XX°±
ANGLES±1°	.XXX°±
UNITS:	mm

PART NO: TTR66160155-2400

**XFCN 兴飞连接器**

TITLE: PCB SOLDERING TERMINAL

0769-82001899  
www.xfconn.com

APPD: Chen ZhiQiang

DWG NO: /

CHKD: Liu Wei

VIEW:

DRAW: Chen HongJiang

SCALE: SHEET: REV

DATE: 2025.02.19

NONE: 1/1: A1

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN

序号	名称	零件编号	材质	数量
2	垫片		SPCC	1
1	插脚		T2 (Y2)	1