






-HOOYA-



NUT



P.C.B LAYOUT



SCHEMATIC

电话：0769-82310511-867

邮箱: hooya89@hooya.hk

SPECIFICATION

1.Rating : DC 30V 3A.

2.Contact resistance: $\leq 50\text{m}\Omega$.

3. Insulation resistance: $\geq 100\text{M}\Omega$ (DC250V).

4. Withstanding voltage: 500VAC .

5.Insertion and extraction force: 3-30N.

6.life test: 5,000 cycles.

7.Operation temperature range: -25℃~85℃.

8. Sign* "is importance dimension.

8					TOLERANCE													
7	SLEEVE	BRASS	1	CuSn-PLATED	UNLESS SPECIFIED													
6	CURVE PIECE	BRASS	1	Sn-PLATED	<1.5: ±0.1mm	ANGULAR ±1°												
5	PIN	BRASS	1	CuSn-PLATED	>1.5~5.0: ±0.25mm													
					>5.0: ±0.3mm		NO	DATE	REVISIONS					BY	APPD			
4	COVER	PBT	1	BLACK	TITLE: DC JACK					UNIT : MM	ROHS	DWN						
3	FLAT PIECE	BRASS	1	Sn-PLATED	MODEL:DC-005M-2.0-PU-04					SCALE: 1:1	COMPLIANT	CHK'D						
2	SPRING	PHOSPHOR BRONZE	1	Sn-PLATED	 HOOYAELEC.COM 皓宇 东莞市弘皓电子有限公司										APPD			
1	HOUSING	PBT	1	BLACK														
NO.	PART NAME	MATERIAL	QTY	FINISHING											PRO.AGL:		REV :A0	