

标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

A

B

C

D

E

F

G

A

B








C

D


E

F

G



PCB Layout




SPECIFICATION (技术要求)

1. Operating Temperature (环境温度): -25℃~85℃
2. Voltage Rating (额定电压): 50V AC/DC
3. Current Rating (额定电流): 0.5A
4. Contact Resistance (接触电阻): 30mΩ
5. Insulation Resistance (绝缘电阻): 100MΩ
6. Dielectric Withstanding Voltage (耐电压): 500V AC Min
7. Insertion/Withdrawal Force (插拔力): 3-50N
8. Life Time (mating cycles) 寿命: >1000 Cycles
9. SIGNAL LOSS<1dB IN BOTH VHF, UHF BAND.
10. NOMINAL IMPEDANCE : 75 OHMS.
11. OPERATING FREQUENCY : 0-2 GHZ.

注: 铆接头拉拔力测试35kg, 无脱离。

3	F头	锌合金	D. Ni	
3	IEC母头	冷扎板	D. Ni	
2	支架	冷扎板	D. CuSn	
1	绝缘体	PPS	棕色	
序 号	品 名	材 质	电镀/颜色	备 注

 深圳市虹成电子有限公司		品 名 TITLE		屏蔽罩	
		料 号 PART NO		HC-PBZ-R10401	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1		
. XX±0.20 X±0.40		单 位 UNIT	MM	制 图 DRAW	AhYe
. X±0.30 ANGULAR: ±2°		张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云
		版 本 REV	A	批 准 APPROVE	赵亮亮

