




N = Number of poles
Dim A = $N \times 8.25 + 2.0$
Dim B = $(N - 1) \times 8.25$

	Dim A	Dim B
4P	± 0.30	± 0.30
5P-8P	± 0.40	± 0.40
9P-16P	± 0.50	± 0.50
17P-23P	± 0.60	± 0.60
24P-30P	± 0.80	± 0.80



SIGN	DATE	DESCRIPTION	APPROVER
△	10/30'12	Change the dimensional tolerance	Jacky
△	10/30'12	Change the screw plating specification	Jacky
△	10/30'12	Change the electrical specification	Jacky
△	06/03'14	change the structure	Guoxue
△	06/03'14	Change the dimensional tolerance	Guoxue
△	08/25'14	The dimensional tolerance is changed from 15.4 ± 0.30 to 15.4 ± 0.50	Airy min

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

MATERIALS ELECTRICAL

RATED VOLTAGE & CURRENT:

300 V, 20 A

WITHSTAND VOLTAGE:

AC 2000 V/Min

INSULATION RESISTANCE:

1000 MΩ OR MORE AT DC 500 V

△ OPERATING TEMPERATURE RANG:

-40 °C ~ +115 °C

SCREW TORQUE VALUE:

7 Lb-In.

WIRE RANGE:

22 - 12 AWG

1) MOLDED PARTS:

POLYIMIDE 66, UL 94 V-0 BLACK

2) TERMINAL:

BRASS, 0.8t

△ 3) TERMINAL SCREWS:

STEEL, M3

4) COVER MATERIAL:

PC

APPROVAL:

PART No.:

Critical dimension:

YK 402 xx 2 x x 00G

NO. OF POLES

04: 4 POLES

05: 5 POLES

06: 6 POLES

...

30: 30 POLES

G:RoHS compliant(lead<4%)
in copper alloy

MARK

0: "@" MARK

1: "ANY" MARK

TERMINAL & SCREW PLATED

0: TERMINAL & SCREW: G/F

△ 1: TERMINAL: G/F, SCREW: Zinc

2: TERMINAL: Sn, SCREW: G/F

△ 3: TERMINAL: Sn, SCREW: Zinc

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		YK-402 W/O Flange & With Cover Series (4P-30P)			
PART NO.	YK402xx2xx00G			DWG NO.	8YK0001-402
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Airy min 2014.08.25	Airy min 2014.08.25		Tolerance
				UNIT: mm	X. ± 0.50
				SCALE: NONE	X.X ± 0.30
					X.XX ± 0.10
					X° $\pm 1^\circ$

SHEET: 01/01 REV.: E