

特 性 FEATURES

- 外形尺寸 L34×W19×H27.8mm　Dimensions L34×W19× H27.8mm
- 66A 触点载流能力　66A contact current carrying capacity
- 触点间隙≥ 2.4mm　Contact clearance ≥ 2.4mm
- 适用于太阳能光伏逆变器、充电桩等领域　Suitable for solar photovoltaic inverters, charging piles and other fields
- 对标松川 117L　Benchmark Matsukawa 117L

触点参数 CONTACT PARAMETERS

触点形式 Contact Arrangement	1A
触点材料 Contact Material	银合金 Silver Alloy
接触电阻 Contact Resistance(初始 Initial)	≤100mΩ （at 1A 6VDC）
最大切换电流 Max. Switching Current	66A
最大切换电压 Max. Switching Voltage	600VAC
最大切换功率 Max. Switching Power	18282VA
电气寿命 Electrical Life	≥1×10^3次 Ops (66A 277VDC，阻性负载 Res. Load，1s On: 9s Off)
	≥1x10^4次 Ops（接接通 20A，载流 66A，断开 20A，600VAC,阻性，85℃，1s 通 9s 断。Making 20A, loading66A, breaking 20A，600VAC, Res. load，85℃，1s On: 9s Off.）
机械寿命 Mechanical Life	≥1×10^6 次 Ops

备注：电气寿命数据仅做参考，以最终产品确认规格书为准。

Notes：The electrical life data is only for reference, and the final product confirmation specification shall prevail.

性能参数 CHARACTERISTICS

绝缘电阻 Insulation Resistance	1000MΩ（500VDC）
介质耐压 Dielectric Strength	触点与线圈间 Between Coil & Contacts: 4000VAC 1min
	断开触点间 Between Open Contacts: 2000VAC 1min
动作时间 Operate Time	≤30ms
释放时间 Release Time	≤10ms
环境温度 Ambient Temperature	-40℃~+85℃
振　　动 Vibration Resistance	10Hz~55Hz 1.5mm 双振幅(DA)
冲　　击 Shock Resistance	稳定性 Functional: 98m/s^2(10G)
	强　度 Destructive: 980m/s^2(100G)
引出端方式 Terminal Form	印制板式 PCB
封装形式 Construction	塑封型 Plastic sealed
重　　量 Unit Weight	约 Approx. 51g

线圈保持电压 COIL HOLDING VOLTAGE

线圈功率 Coil Power	3.8W
保持电压 Holding Voltage	40% to 70%UN (at 23℃) 40% to 55%UN (at 85℃)

备注 Notes:

(1) 线圈保持电压为线圈施加额定电压 100ms 以上的线圈电压。The coil holding voltage is the voltage of coil after being applied rated voltage for 100ms

(2) 继电器线圈不允许长时间施加超过保持电压的上限值，防止继电器过热烧毁。The relay coil is not allowed to exceed the upper limit of the holding voltage for a long time, preventing the relay from overheating and burning.

线圈规格表 COIL DATA (@23℃)

额定电压 Rated Voltage VDC	动作电压 Operate Voltage VDC	释放电压 Release Voltage VDC	最大允许电压 Max. Voltage VDC	线圈电阻 Coil Resistance Ω±10%
9	≤7.2	≥0.45	10.8	21
12	≤9.6	≥0.6	14.4	38
24	≤19.2	≥1.2	28.8	152

©浙江美硕电气科技有限公司版权所有，本公司保留所有权利。Zhejiang Meishuo Electrical Technology Co., Ltd. All rights reserved.

安全认证 APPROVALS


安全认证 Approvals	UL	TUV	CQC	VDE
证书编号 Certificate Number	/	/	/	/

订货标记示例 ORDERING INFORMATION


	ME121	-S	-1	A	-F	12VDC
产品型号 Model	ME121					
封装形式 Construction	S: 塑封型 Sealed Type					
触点组数 Contact Group	1: 1 组 Group					
触点形式 Contact Form	A: 常开 NO					
绝缘等级 Insulation Class	F: F 级 Class					
线圈电压 Coil Voltage	9: 9VDC； 12: 12VDC； 24: 24VDC					

外形尺寸、接线图、安装孔尺寸 OUTLINE DIMENSIONS,WIRING DIAGRAM AND PCB LAYOUT (单位 Unit: mm)


外形尺寸 Outline Dimensions




安装孔尺寸 PCB Layout（底视 Bottom View）



接线图 Wiring Diagram（底视 Bottom View）





备注 REMARK:

1) 产品部分外形尺寸未注尺寸公差，当外形尺寸≤1mm，公差为±0.2mm；当外形尺寸在 1~5mm 之间时，公差为±0.3mm；当外形尺寸＞5mm 时，公差为±0.4mm。
   In case of no tolerance shown in outline dimension: outline dimension ≤1mm, tolerance should be ±0.2mm; outline dimension ＞1mm and ≤5mm, tolerance should be ±0.3mm; outline dimension ＞5mm, tolerance should be ±0.4mm.
2) 安装孔尺寸中未注尺寸公差的均为±0.1mm。
   The tolerance without indicating for PCB layout is always ±0.1mm.

声明 STATEMENT：

1. 本产品规格书仅供客户使用时参考，若有更改，恕不另行通知。
   This product specification for client's reference, if any change without notice.
2. 对美硕而言，不可能评定继电器在每个具体应用领域的所有性能参数要求，因而客户应该根据具体的使用条件选择与之相匹配的产品，若有疑问，请与美硕联系获取更多的技术支持。但产品选型责任仅由客户负责。
   For Meishuo, cannot require evaluation of relays in each specific application of all the performance parameters, so customers should be selected according to the matching conditions for the use of specific products, if you have any questions, please contact us and get more technical support. However, product selection responsibility only by the customer.

©浙江美硕电气科技有限公司版权所有，本公司保留所有权利。Zhejiang Meishuo Electrical Technology Co., Ltd. All rights reserved.