926477-1 ✔ ACTIVE

AMPMODU | AMPMODU IV/V

TE Internal #: 926477-1

Retention Plug, Black, Polycarbonate GF, AMPMODU IV/V

View on TE.com >

Connectors > Connector Accessories > Connector Hardware







Hardware Accessory Function: **Latching, Locking & Retention**

Connector Hardware Accessory Type: **Retention Plug**

Primary Product Color: **Black**

Primary Product Material: **Polycarbonate GF**

Operating Temperature (Max): **105 °C [221 °F]**

Features

Product Type Features

Hardware Accessory Function	Latching, Locking & Retention
Connector Hardware Accessory Type	Retention Plug

Body Features

Primary Product Color	Black
Primary Product Material	Polycarbonate GF

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Quantity	15000
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Perfluorobutane sulfonic acid (PFBS) and its salts (.2% in Component Part) **Article Safe Usage Statements:** Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 926476-3
MOD 4 HSG



TE Part # 926475-3
03P MODU 4 HSG.S.R.



TE Part # 926475-4
MOD 4 HSG



TE Part # 926476-4
2X4P MODU 4 HSG.



TE Part # 926476-6
MOD 4 HSG



TE Part # 1-926476-0
MOD 4 HSG



TE Part # 926475-8
MOD 4 HSG



TE Part # 1-926475-0
MOD 4 HSG



TE Part # 1-926476-7
MOD 4 HSG



TE Part # 926475-7
MOD 4 HSG



TE Part # 926475-5
MOD 4 HSG



TE Part # 926476-8
MOD 4 HSG



TE Part # 926475-6
MOD IV HSG SR 6 POS



TE Part # 926476-5
MOD 4 HSG



TE Part # 1-926476-3
MOD 4 HSG



TE Part # 926476-7
MOD 4 HSG



TE Part # 3-926475-0
MOD 4 HSG



TE Part # 926476-9
MOD 4 HSG




TE Part # 1-926475-2
MOD 4 HSG



TE Part # 1-926475-3
MOD 4 HSG

Also in the Series | AMPMODU IV/V



Backplane Connector Housings(1)



Connector Caps & Covers(15)




Connector Contacts(321)



Connector Hardware(13)



Insertion & Extraction Tools(4)



PCB Headers & Receptacles(931)



Rectangular Connector Housings(5)



Standard Rectangular Connectors(7)



Wire-to-Board Connector Assemblies & Housings(436)

Customers Also Bought



TE Part #926476-3
MOD 4 HSG



TE Part #7-1625890-1
2W SM M/OX 5% 82R



TE Part #926476-4
2X4P MODU 4 HSG.



TE Part #926476-6
MOD 4 HSG



TE Part #926476-8
MOD 4 HSG



TE Part #926475-6
MOD IV HSG SR 6 POS



TE Part #926476-5
MOD 4 HSG



TE Part #1241381-1
AMP MCP 1.5K, CONTACT, SWS, (LP)

TE Part #2-1768423-0
LBG-U-03417/1/ETI3344

Documents

Product Drawings

RETENTION FORK

English

CAD Files

Customer View Model

ENG_CVM_926477-1_P0F1.3d_igs.zip

English

Customer View Model

ENG_CVM_926477-1_P0F1.3d_stp.zip

English

Customer View Model

ENG_CVM_926477-1_P0F1.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Product Specification

English