



RoHS compliant
by exemption








PCB hole pattern, mounting side





3	5	Signal contact	S5 / Brass	0.8µm Au
2	1	Shell	Steel	tin plated
1	1	Insulator	PBT (-55°C to +130°C) acc. UL94V-0	green
No.	*St.*	*Part*	*Type Description/Material*	*Surface plating/Colour/Class*

FUNCTIONAL SYMBOLS
= 0
= 0
= 0

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS: mm
SCALE: 2:1
MEASUREMENTS WITHOUT TOLERANCE ACC. TO: ISO 2768-m

REV.	CH.-NO.
3	24410
2	24130
1	

CURRENT REVISION
DRWN: DRAWN BY msteinbrueck 07-08-2023
APPR: APPR BY fvetter 17-08-2023

INITIAL REVISION
DRWN: DRAWN BY ADenzinger 23-03-2006
APPR: APPR BY skusber 24-03-2006

molex

FCT D-Sub Mixed-Layout Connector

PRODUCT CUSTOMER DRAWING

REPLACEMENT FOR:	FRIST ANGLE PROJECTION	DRAWING	MATERIAL NUMBER	REVISION
1731070095_Rev. A		A3-SIZE	1731070095	3

DOCUMENT NUMBER	CUSTOMER	SHEET NUMBER
FM7W2S5-K121	GENERAL MARKET	1 OF 1

COMMENT:
ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING, WITHOUT OUR PRIOR CONSENT, IT MAY NEITHER BE DUBLICATED NOR MADE AVAILABLE TO A THIRD PARTY, AND IT ALSO MAY NOT BE IMPROPERLY USED BY TE RECEIVER, OR A THIRD PARTY.