



SIGN	DATE	DESCRIPTION	APPROVER
⚠	2014.09.10	Upgrade the picture	Airy min

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!









PCB Layout

Material:

- Item 1 Insulator(Cover): Thermoplastic (UL94V-0)
- Item 2 Insulator(housing): Thermoplastic (UL94V-0)
- Item 3 Spring clamp: Stainless steel
- Item 4 Solder Pin (The fourth layer) : Brass, Tin plated
- Item 5 Solder Pin (The third layer) : Brass, Tin plated
- Item 6 Solder Pin (The second layer) : Brass, Tin plated
- Item 7 Solder Pin (The first layer) : Brass, Tin plated
- Item 8 Insulator(pad board): Thermoplastic (UL94V-0)

Electrical:	cULus
Voltage rating:	300V
Current rating:	10A
Wire range:	
Solid wire(AWG):	12-28
Stranded wire(AWG):	12-28
Wire strip length:	6-7mm
Withstanding Voltage:	1.6KV
Operating temperature:	-40°C to +115°C
Soldering temperature:	250°C±10°C/5 Sec
Safety Approval:	c UL us
Critical dimension:	▽

HS xx 1 0 x 1 xxxx G

- No. OF POLES
  - 08: 4×2 POLES
  - 60: 4×15 POLES
  - 64: 4×16 POLES
- COLOR
  - 0: BLACK
  - 5: GREEN (RAL 6018/T)
  - 6: BLUE
  - 8: GREY (RAL 7004/P)
- G: Pb<40000ppm
- 0000: "@" Logo (Standard)
- 000A: "ANYTEK" Mark

Any special item by customer requst. please contact sales department.

N = Number of poles.

⚠ Dim.A = N*7.5−1.5

Dim.B = (N−1)*7.5

POLE	4×2 ~ 4×4	4×5 ~ 4×8	4×9 ~ 4×12	4×12 ~ 4×16
Dim.A	±0.15	±0.25	±0.35	±0.45
Dim.B	±0.15	±0.25	±0.30	±0.40

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	HS 7.5mm Series (Solder pins staggered by half the pin spacing)					
PART NO.	HSxx10x1xxxxG			DWG NO.	8HS0202	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance
		Airy min 2014.09.10	Airy min 2014.09.10	UNIT: mm SCALE: NONE SHEET: 01/01	REV.: C	X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°