160337-2 ✔ ACTIVE

TE Internal #: 160337-2

Closed Ring Tongue Terminal, 18 – 14 AWG, M6 Stud, 6.4 mm [.252 in] Stud Diameter, Open Barrel, Straight, Tin Plating, Uninsulated

View on TE.com >

Terminals & Splices > Ring Terminals







Ring Terminal Product Type: **Closed Ring Tongue Terminal**

Wire Size: **1618 – 4107 CMA**

Stud Size: **M6**

Features

Configuration Features

Number of Holes	1

Body Features

Product Weight	.983 g

Mechanical Attachment

Wire Insulation Support	With

Industry Standards

Government Qualified Terminal	No

Packaging Features

Packaging Quantity	6000
Packaging Method	Strip/Reel

Contact Features

Contact Base Material	Brass
Barrel Type	Open
Terminal Orientation	Straight
Terminal Plating Material	Tin
Contact Underplating Material	Nickel

Dimensions

	.098 in
Wire Size	1618 – 4107 CMA
Stud Diameter	6.4 mm[.252 in]
Tongue Thickness	.51 mm[.02 in]
Product Length	19.81 mm[.78 in]
Barrel Inside Diameter	1.65 mm, 2.79 mm[.11 in][.065 in]
Compatible Insulation Diameter (Max)	.3 mm[.118 in]
Compatible Insulation Diameter Range	2.5 – 3 mm[.098 – .118 in]

Product Type Features

Shape Description	Circular/Oval
Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	M6
Sealable	No
Compatible With Discrete Wire Type	Stranded
Wire Insulation Support Retention Type	Insulation Support

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Operation/Application

Compatible With Wire Base Material	Copper

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241)

	Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Compatible Parts



TE Part # 62638-1
RING TONGUE 22-20 AWG TPBR



TE Part # 2151372-2
OCEAN-2.0-APPLICATOR-S-070F130O-RSA




TE Part # 160787-1
RING TONGUE IS 18-14 AWG .0840 X .940 BR



TE Part # 2151370-1
OCEAN_2.0_Applicator-E-130F180F-REM



TE Part # 2151370-2
OCEAN_2.0_Applicator-E-130F180F-REA



TE Part # 7-2151370-7
OCEAN_2.0_SPARE_PART_KIT-130F180F

Customers Also Bought



TE Part #55148-1
TERMINAL,PIDG R 22-16 10



TE Part #1-1609112-4
15CBE1=F8274



TE Part #280223-2
FASTON 375 ASY REC 4-6MM2 0.5X27.0 TPBR



TE Part #1742999-1
250 FASTON,FLAG,REC.,18-14 AWG, BR




TE Part #1-368889-1
WIRE SEAL FOR EJ MK-II(+) BLUE




TE Part #ANT-DB1-LP-RM-01-N
Antenna Directional Tri-Band Hi-Gain N



TE Part #2-1564559-1
4POS, MCON 1.2 LL TAB SEALED COD B



TE Part #174264-2
ECONO-J MK-2 CAP HSG 6P



TE Part #171631-1
E-J MK-2 070 TAB CONT



TE Part #FTRA6971M5PB-001
OMNI,Ph,PMT,698-7125MHz

Documents

Product Drawings

RING TONGUE IS 18-14 0.295 X .940 TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_160337-2_H.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_160337-2_H.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_160337-2_H.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Product Specification

English

Product Specification

English

Product Specification

English