


UNIT OF MEASURE	A	B	C	D	E	L		MAX. BUNDLE DIA.	MIN. TENSILE STRENGTH
INCHES	.275	.295	.183	2.37	.051	11.83		3.0	50 lbs.
MM	6.99	7.49	4.65	6.02	1.30	300.		76.2	22.68 kg.

THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE BY YOU TO OTHER THAN AMP PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM AMP INCORPORATED, HARRISBURG, PA.



NOTES:

1. MOISTURIZED 1 TO 2.5% WATER.
2. PACKAGED IN HEAT SEALED 3 MIL POLYBAG WITH LABEL PER DWG 404707.
3. MIL No. MS3367-7.

APC ENGINEERING

JUL 13 1990

ISSUED BY *CLC*

CUSTOMER DRAWING UNPUBLISHED

2-604751-9	NATURAL 1000 TY3AM
2-604751-0	BLACK 1000 TY3AMB
1-604751-9	NATURAL 100 TY3AC
1-604751-0	BLACK 100 TYACB
604751-2	BLACK 1 (NO PKG.)
604751-1	NATURAL 1 (NO PKG.)

LOC	DWG SIZE	PART No.	DESCRIPTION	ITEM NO
D				
DIST	REVISION OF EACH ASSY NO. (WHEN BLANK, USE DWG REVISION)			
1	QTY. REQ'D. PER ASSY. PARTS LIST			

MATERIAL	NYLON 6/6	HEAT TREAT	FINISH
DIMENSIONS ARE IN INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DRAWN BY:	DATE:
2 PL DEC ±	3 PL DEC ± .039	AD-TEK/VL	6/26/90
4 PL DEC ±	ANGLES ±	CHECK BY:	RELEASE:
SURF TEXTURE: J	REMOVE BURRS. BREAK SHARP EDGES. .015 R. MAX.	Bjm 6/90	J. Havel 6/90
NAME:		AMP INCORPORATED Harrisburg, Pa.	
CABLE TIE 11-3/4 INCH			
B1	REVISED PER ECR-25-253648	SA MDP	03SEP2025
B	ECN 062890	THN	6/90
P	F	LTR	REVISION RECORD
APP	DATE	SCALE: A	DRAWING No.: 604751
SHEET	1 OF 1	REV.	B1