2300281-1 ✔ ACTIVE

zQSFP+/QSFP28


TE Internal #: 2300281-1

QSFP28/56, Cage Assembly, 19mm [.748in] Centerline, Operating Temperature Range -40 – 85 °C [-40 – 185 °F], 2 Ports, Port Matrix Configuration 1 x 2

View on TE.com >

Connectors > Pluggable IO Connectors & Cages







Form Factor: **QSFP28/56**

Pluggable I/O Product Type: **Cage Assembly**

Centerline (Pitch): **19 mm [.748 in]**

Operating Temperature Range: **-40 – 85 °C [-40 – 185 °F]**

Number of Ports: **2**

Features

Industry Standards

UL Flammability Rating	UL 94V-0

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
Termination Post & Tail Length	2.05 mm[.081 in]

Dimensions

PCB Thickness (Recommended)	1.57 mm[.062 in]

Operation/Application

Heat Sink Compatible	No

Contact Features

PCB Contact Termination Area Plating Material	Tin

Packaging Features

Packaging Method	Box & Tray

Configuration Features

Number of Rear EONs per Port Column	0
Number of Ports	2
Port Matrix Configuration	1 x 2

Housing Features

Cage Material	Nickel Silver
Centerline (Pitch)	19 mm[.748 in]

Product Type Features

Cage Type	Ganged
Form Factor	QSFP28/56
Pluggable I/O Product Type	Cage Assembly

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]

Other

Included Lightpipe	No
EMI Containment Feature Type	Internal/External EMI Springs
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as

EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 2829040-7
QSFP IB EDR, 26AWG, 2.0M



TE Part # 2829040-8
QSFP IB EDR, 26AWG, 3.0M



TE Part # CAT-C11-Q17
QSFP56 to QSFP56 Cable Assembly: 26 AWG



TE Part # CAT-Q17-N49033
QSFP56-Two QSFP56 Cable Assembly: 30 AWG



TE Part # CAT-C11-Z8
QSFP28 to QSFP28 Cable Assembly: 26 AWG



TE Part # 2829040-4
QSFP IB EDR, 30AWG, 1.0M



TE Part # 2821033-8
QSFP TO [4]SFP+, 28G, 1M, 33AWG



TE Part # 1551920-2
zQSFP+ connector assembly



TE Part # CAT-Q17-N490325
QSFP56 to QSFP56 Cable Assembly: 30 AWG



TE Part # 2829040-2
QSFP IB EDR, 33AWG, 1.0M



TE Part # 2185234-1
ASSY, SEATING TOOL, QSFP28



TE Part # CAT-Q17-N49011
QSFP56-Four SFP56 Cable Assembly: 30 AWG



TE Part # CAT-C11-Z806726
QSFP28 to QSFP28 Cable Assembly: 30 AWG



TE Part # 2829040-6
QSFP IB EDR, 30AWG, 2.0M



TE Part # CAT-C11-N49
QSFP28-Two QSFP28 Cable Assembly: 30 AWG



TE Part # CAT-C11-N490333
QSFP28-Four SFP+ Cable Assembly: 30 AWG




TE Part # CAT-Q17-N490333
QSFP56-Four SFP56 Cable Assembly: 26 AWG



TE Part # CAT-C11-N490325
QSFP28-Four SFP+ Cable Assembly: 26 AWG


Also in the Series | zQSFP+/QSFP28



Heat Sinks(7)




Pluggable I/O Cable Assemblies(78)




Pluggable IO Connectors & Cages(424)

Customers Also Bought




TE Part #10142048-22
HTU31D I.C 31D RH/T DIGITAL R5000



TE Part #2170903-1
RECEPTACLE HM-EZD+, 4PAIRS 10COLUMNS



TE Part #2-1926739-5
AssyMinipak Hdl25s10pRARecptSc



TE Part #5223979-1
UPM GUIDE MODULE



TE Part #2170088-1
ZSFP+ Connector,30u"



TE Part #2110487-1
QSFP Cage, Solder Leg, No HS Opening



TE Part #2110819-1
QSFP+ Enh EVERCLEAR PT Conn



TE Part #2170790-3
CAGE ASSY, 1X4, QSFP28, SPRING, HS, LP



TE Part #2317010-1
ZSFP+ 1X2 CAGE BELLY TO BELLY

TE Part #2360945-2
RCPT CONN R/A SMT 76 POSN QSFP-DD, W/ PI

Documents

Product Drawings

CAGE ASSEMBLY, 1X2, QSFP28, SPRING

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2300281-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2300281-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2300281-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Application Specification

English

Application Specification

English