




LOC	DIST	REVISIONS					
AF	50	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A2	REVISED PER ECR-07-022971	28SEP07	JR	GJ



- 1 SPECIFICATION MAGNET WIRE:
#12-#23 AWG, .022-.081 [0.56-2.06mm] DIA COPPER.
- 2 SPECIFICATION MALE BLADE: .031-.033 [0.79-0.84mm] THICK HAVING A 10° X .030 LONG SWAGE AT THE END. BLADE TO BE .100 [2.5mm] MINIMUM WIDTH AND EXCEPT FOR THE SWAGE, HAVE A UNIFORM THICKNESS WITHOUT A HOLE OR DIMPLE.
- 3 POCKET RECOMMENDATION: 1601436.
- 4 TERMINAL APPLICATION TO COMPLY WITH TYCO ELECTRONICS SPECIFICATION 114-13210, FIG 5.
- 5 POST TIN PLATE OVER NICKEL UNDERPLATE.
- 6 PRELIMINARY - NOT FOR PRODUCTION.



6	4-1601232-2
	2-1601232-2
	1601232-2
	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN MICHAEL S. FEHER 29AUG2006	 Tyco Electronics Corporation Harrisburg, PA 17105-3608				
DIMENSIONS: INCHES [mm]		CHK GENE JACONO 29AUG2006	NAME MEDIUM RANGE WIRE TO BLADE SIAMEZE TERMINAL —				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:						APVD GENE JACONO 29AUG2006
	0 PLC ± — 1 PLC ± — 2 PLC ± .01[0.25] 3 PLC ± .005[0.13] 4 PLC ± — ANGLES ± 2°						PRODUCT SPEC 108-2239
MATERIAL BRASS, SPRING HARD		FINISH 	APPLICATION SPEC — 	SIZE A2	CAGE CODE 00779	DRAWING NO C=1601232	RESTRICTED TO —
CUSTOMER DRAWING			SCALE 4:1		SHEET 1 of 1		REV A2