


**CUI INC**

a bel group

**date** 11/02/2022

**page** 1 of 7


**SERIES:** PSK-60 | **DESCRIPTION:** INTERNAL AC-DC POWER SUPPLY

**FEATURES**

- universal input voltage range (85~264 VAC)
- IEC/EN/UL 62368 certified
- meets CISPR32/EN 55032 Class B without external components
- 4,000 VAC isolation rating
- short-circuit, over-current, over-voltage protections



| MODEL     | output voltage | output current max | output power max | ripple and noise max | efficiency |
|-----------|----------------|--------------------|------------------|----------------------|------------|
|           | (Vdc)          | (A)                | (W)              | (mVp-p)              | typ (%)    |
| PSK-60-5  | 5              | 10.0               | 50               | 120                  | 84         |
| PSK-60-12 | 12             | 5.0                | 60               | 120                  | 87         |
| PSK-60-15 | 15             | 4.0                | 60               | 120                  | 88         |
| PSK-60-24 | 24             | 2.5                | 60               | 120                  | 89         |
| PSK-60-48 | 48             | 1.25               | 60               | 120                  | 90         |

**PART NUMBER KEY**


## INPUT

| parameter                 | conditions/description   | min | typ      | max | units |
|---------------------------|--------------------------|-----|----------|-----|-------|
| voltage                   | ac input                 | 85  |          | 264 | Vac   |
|                           | dc input                 | 100 |          | 370 | Vdc   |
| frequency                 |                          | 47  |          | 63  | Hz    |
| current                   | at 115 Vac               |     |          | 1.8 | A     |
|                           | at 230 Vac               |     |          | 1.0 |       |
| inrush current            | at 115 Vac<br>at 230 Vac |     | 45<br>90 |     | A     |
| no load power consumption | at 230 Vac               |     |          | 0.5 | W     |

## OUTPUT

| parameter                  | conditions/description | min | typ        | max    | units   |
|----------------------------|------------------------|-----|------------|--------|---------|
| capacitive load            | 5 Vdc output           |     |            | 20,000 | $\mu$ F |
|                            | 12 Vdc output          |     |            | 4,000  |         |
|                            | 15 Vdc output          |     |            | 3,000  |         |
|                            | 24 Vdc output          |     |            | 1,800  |         |
|                            | 48 Vdc output          |     |            | 470    |         |
| initial set point accuracy | at full load           |     | $\pm 2$    |        | %       |
| line regulation            | rated load             |     | $\pm 0.5$  |        | %       |
| load regulation            | 0%~100% load           |     | $\pm 1.0$  |        | %       |
| hold-up time               | at 115 Vac             |     | 8          |        | ms      |
|                            | at 230 Vac             |     | 65         |        |         |
| temperature coefficient    |                        |     | $\pm 0.02$ |        | %/°C    |



## PROTECTIONS

| parameter                | conditions/description            | min | typ | max | units |
|--------------------------|-----------------------------------|-----|-----|-----|-------|
| over voltage protection  | 5 Vdc output, clamp               |     |     | 9   | Vdc   |
|                          | 12 Vdc output, clamp              |     |     | 16  |       |
|                          | 15 Vdc output, clamp              |     |     | 25  |       |
|                          | 24 Vdc output, clamp              |     |     | 35  |       |
|                          | 48 Vdc output, clamp              |     |     | 60  |       |
| over current protection  | auto recovery                     | 110 |     |     | %     |
| short circuit protection | hiccup, continuous, auto recovery |     |     |     |       |



## SAFETY & COMPLIANCE

| parameter                     | conditions/description                                                                                             | min     | typ | max | units |
|-------------------------------|--------------------------------------------------------------------------------------------------------------------|---------|-----|-----|-------|
| isolation voltage             | input to output                                                                                                    | 4,000   |     |     | Vac   |
| safety approvals              | UL/cUL, EN, IEC 62368                                                                                              |         |     |     |       |
| safety class                  | Class II                                                                                                           |         |     |     |       |
| EMI/EMC                       | CISPR 32/EN 55032 Class B                                                                                          |         |     |     |       |
| ESD                           | IEC/EN 61000-4-2 Contact $\pm 6$ KV/Air $\pm 8$ KV, perf. Criteria B                                               |         |     |     |       |
| radiated immunity             | IEC/EN 61000-4-3 10 V/m, perf. Criteria A                                                                          |         |     |     |       |
| EFT/burst                     | IEC/EN 61000-4-4 $\pm 4$ KV, perf. Criteria B                                                                      |         |     |     |       |
| surge                         | IEC/EN 61000-4-5 line to line $\pm 2$ KV/line to ground $\pm 4$ KV, perf. Criteria B (see recommended EMC circuit) |         |     |     |       |
|                               | IEC/EN 61000-4-5 $\pm 1$ KV line to line, perf. Criteria B                                                         |         |     |     |       |
| conducted immunity            | IEC/EN 61000-4-6 10 Vr.m.s, perf. Criteria A                                                                       |         |     |     |       |
| voltage dips and interruption | IEC/EN 61000-4-11 0%, 70%, perf. Criteria B                                                                        |         |     |     |       |
| MTBF                          | per MIL-HDBK-217F at 25 °C                                                                                         | 300,000 |     |     | hours |
| RoHS                          | yes                                                                                                                |         |     |     |       |

## DERATING CURVES

**TEMPERATURE DERATING CURVE****INPUT VOLTAGE DERATING CURVE  
(25 °C)**

## EFFICIENCY CURVES

**EFFICIENCY VS INPUT VOLTAGE (Full load)****EFFICIENCY VS OUTPUT LOAD (Vin = 230 Vac)**

## ENVIRONMENTAL

| parameter             | conditions/description | min | typ | max | units |
|-----------------------|------------------------|-----|-----|-----|-------|
| operating temperature |                        | -40 |     | 70  | °C    |
| storage temperature   |                        | -40 |     | 85  | °C    |
| storage humidity      |                        | 0   |     | 95  | %     |

## SOLDERABILITY

| parameter      | conditions/description     | min | typ | max | units |
|----------------|----------------------------|-----|-----|-----|-------|
| wave soldering | 5~10 seconds ( $\pm 5$ °C) |     |     | 260 | °C    |
| manual welding | 3~5 seconds ( $\pm 10$ °C) |     |     | 360 | °C    |

## MECHANICAL


| parameter     | conditions/description                                      | min | typ | max | units |
|---------------|-------------------------------------------------------------|-----|-----|-----|-------|
| dimensions    | 87.00 x 52.00 x 29.50 (board mount)                         |     |     |     | mm    |
|               | 135.00 x 70.00 x 37.90 (chassis mount)                      |     |     |     | mm    |
|               | 137.00 x 70.00 x 42.40 (DIN-rail)                           |     |     |     | mm    |
| weight        | board mount                                                 |     | 210 |     | g     |
|               | chassis mount                                               |     | 290 |     | g     |
|               | DIN-rail                                                    |     | 360 |     | g     |
| cooling       | free air convection                                         |     |     |     |       |
| case material | black plastic, flame-retardant and heat-resistant (UL94V-0) |     |     |     |       |

## MECHANICAL DRAWING (BOARD MOUNT)

units: mm [inch]

pin diameter tolerance:  $\pm 0.1$  [ $\pm 0.004$ ]


| PIN CONNECTIONS |          |
|-----------------|----------|
| PIN             | Function |
| 1               | AC(L)    |
| 2               | AC(N)    |
| 3               | +Vo      |
| 4               | -Vo      |



## MECHANICAL DRAWING (CHASSIS MOUNT)

units: mm [inch]  
 tolerance:  $\pm 1.00$  [ $\pm 0.040$ ]  
 wire range: 24 - 12 AWG  
 tightening torque: 0.4 N·m


| PIN CONNECTIONS |          |
|-----------------|----------|
| PIN             | Function |
| 1               | AC(L)    |
| 2               | NC       |
| 3               | AC(N)    |
| 4               | +Vo      |
| 5               | -Vo      |
| 6               | NC       |
| 7               | NC       |
| 8               | NC       |



## MECHANICAL DRAWING (DIN-RAIL MOUNT)

units: mm [inch]  
 tolerance:  $\pm 1.00$  [ $\pm 0.040$ ]  
 wire range: 24 - 12 AWG  
 tightening torque: 0.4 N·m  
 installed on DIN-RAIL TS35

| PIN CONNECTIONS |          |
|-----------------|----------|
| PIN             | Function |
| 1               | AC(L)    |
| 2               | NC       |
| 3               | AC(N)    |
| 4               | +Vo      |
| 5               | -Vo      |
| 6               | NC       |
| 7               | NC       |
| 8               | NC       |



## APPLICATION CIRCUIT

Figure 1




Table 1

| Recommended External Circuit Components |           |             |                          |         |          |
|-----------------------------------------|-----------|-------------|--------------------------|---------|----------|
| Part no.                                | C1        | C2          | FUSE                     | MOV     | TVS      |
| PSK-60-5                                | 1 $\mu$ F | 680 $\mu$ F | 3.15A/250V,<br>slow-blow | S10K300 | SMBJ7.0A |
| PSK-60-12                               |           | 330 $\mu$ F |                          |         | SMBJ20A  |
| PSK-60-15                               |           | 330 $\mu$ F |                          |         | SMBJ20A  |
| PSK-60-24                               |           | 200 $\mu$ F |                          |         | SMBJ30A  |
| PSK-60-48                               |           | 100 $\mu$ F |                          |         | SMBJ64A  |

## EMC RECOMMENDED CIRCUIT

Figure 2




Table 2

| Component | Reccomended value               |
|-----------|---------------------------------|
| FUSE      | 3.15A/250V, slow-blow, required |
| MOV1      | S20K300                         |
| MOV2/MOV3 | S10K300                         |
| GDT       | EM3600XS                        |
| CX        | 0.22 $\mu$ F / 275 Vac          |
| CY1, CY2  | 1 nF / 400 Vac                  |
| R1        | 1 M $\Omega$ / 2 W              |
| LDM       | 4.7 $\mu$ H                     |
| LCM       | 2 mH                            |

## REVISION HISTORY

| rev. | description                         | date       |
|------|-------------------------------------|------------|
| 1.0  | initial release                     | 07/14/2020 |
| 1.01 | din-rail mechanical drawing updated | 03/12/2021 |
| 1.02 | figure and circuit drawings updated | 03/25/2021 |
| 1.03 | UKCA mark added                     | 06/06/2022 |
| 1.04 | OVP updated                         | 11/02/2022 |

The revision history provided is for informational purposes only and is believed to be accurate.



**Headquarters**  
20050 SW 112th Ave.  
Tualatin, OR 97062  
**800.275.4899**

Fax 503.612.2383  
**cui.com**  
techsupport@cui.com

CUI offers a two (2) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.